

## Product data sheet

### Characteristics

# 21127

## Eliberare Tensiune - Mx - 220 - 240 V Ac 50 Hz



### Principal

Range of product	Acti 9
Tip produs sau componenta	Bobina de declansare la alimentare cu tensiune
Nume scurt al dispozitivului	MX
[Ie] curent nominal de utilizare	AC-15 3,3 A la 240 V c.a. 50/60 Hz
Tensiune circuit de comanda	220...240 V c.a. 50/60 Hz
Pasi de 9 mm	4

### Suplimentar

Compatibilitate gama	P25M
[Ui] tensiune nominala de izolatie	690 V AC 50/60 Hz conforming to EN/IEC 60947-5-1
[Uimp] tensiune nominala de tinere la impuls	6 kV conformitate cu SR EN 60947-5-1
Semnalizare locala	Indicator de acționare
Mod de montare	Fix
Suport de montare	Sina DIN simetrica, 35 mm
Inaltime	92 mm
Latime	37 mm
Adancime	82 mm
Greutate neta	0,114 kg
Conexiuni - borne	Clamp terminal - 1 cablu(s) 1...2.5 mm <sup>2</sup> - rigid Clamp terminal - 1 cablu(s) 0.75...2.5 mm <sup>2</sup> - flexible Clamp terminal - 1 cablu(s) 0.75...1.5 mm <sup>2</sup> - flexible with ferrule Borna cu clema - 2 cablu(ri) 1...2,5 mm <sup>2</sup> - rigid Borna cu clema - 2 cablu(ri) 0,75...2,5 mm <sup>2</sup> - flexibil Clamp terminal - 2 cablu(s) 0.75...1.5 mm <sup>2</sup> - flexible with ferrule
Cuplu de strangere	1.4 N.m

### Mediu




Standarde	SR EN 60947-5-1
Certificari produs	CEBEC NEMKO FIMKO SEMKO DEMKO
Tropicalizare	2 conformitate cu SR EN 60947-5-1
Umiditate relativa	95 % at 55 °C
Temperatura ambientala de functionare	-20...60 °C
Temperatura de depozitare	-40...80 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Tip unitate a formei de impachetare 1	PCE
Număr de produse în pachet	1
Greutate colet(Lbs)	96 g
Înălțimea formei de impachetare 1	3,7 cm
Latimea formei de impachetare 1	8,2 cm
Lungimea formei de impachetare 1	9,2 cm
Tip unitate a formei de impachetare 2	S01
Numar de unitati in forma de impachetare 2	16
Greutatea formei de impachetare 2	2,024 kg
Înălțimea formei de impachetare 2	15 cm
Latimea formei de impachetare 2	15 cm
Lungimea formei de impachetare 2	40 cm

## Offer Sustainability

Directiva RoHS UE	Conform  <a href="#">Declaratia RoHS UE</a>
Fara metale grele toxice	Da
Fara mercur	Da
Informatii privind scutirea de la RoHS	 Da
Regulamentul RoHS China	 <a href="#">Declaratia RoHS China</a>
WEEE	În Uniunea Europeana, produsele trebuie reciclate respectand sistemul specific de colectare a deeurilor si nu trebuie sa ajunga in pubelele de colectare a deeurilor menajere.

## Garanție contractuală

Garantie	18 luni
----------	---------