

Product data sheet

Characteristics

MGU3.163.25

Intrerupator cap scara 16AX, 1m, fildes



Principal

Gama de produse	Unica
Denumire	Unica (standard estetic)
Tip produs sau componenta	Intrerupator
Prezentare dispozitiv	Mecanism
Tip tehnologie	Electromecanic
Functie de comutare	Cap scara
Numar de clapete	1
Aplicatie a dispozitivului	Control lumini
Culoare	Fildes

Suplimentar

Curent nominal	16 AX
[Ue] tensiune nominala	250 V
Tip retea electrica	C.a.
Frecventa retea electrica	50/60 Hz
Durabilitate electrica	5000 cic
Rezistenta de izolatie	> 5 MΩ la 500 V
Rigiditate dielectrica	2000 V
Capacitatea de rupere la sarcina minima	200 operatii 1.25 In si 1.1 Un, cos phi = 0,3
Distanța de deschidere	> 3 mm
Actuator	Clapeta
Numar module	1 modul
Conexiuni - borne	Borne cu surub
Sectiune cablu	0...4 Mm² rigid cablu 0...4 mm² flexibil cablu
Material	ASA + PC: capac mecanism ABS (nitril acrilic butadiena - stirena): capac mecanism
Mod de fixare	Clipsare
Latime	22,5 mm
Inaltime	45 mm
Adancime	33 mm
Adancime de montaj	21 mm
Greutate neta	0,0218 kg
Temperatura ambientala de functionare	25...35 °C
Temperatura ambietala pentru depozitare	0...50 °C
Standarde	Directiva de joasa tensiune EMC Directiva de compatibilitate electromagnetica EN 60669-1

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mediu

Grad de protectie IP	IP20
Grad de protectie IK	IK01
Caracteristica de mediu	Acetona Benzina Sapun lichid Decolorant Rezistent UV Ulei Alcool Fluid de curatare a geamurilor

Unitati de ambalare

Unitate de masura pentru prima forma de impachetare	PCE
Numar unitati in prima forma de impachetare	1
Inaltime prima forma de impachetare	6,7 cm
Latime prima forma de impachetare	4,4 cm
Lungime prima forma de impachetare	6,8 cm
Greutate prima forma de impachetare	28,0 g
Unitate de masura pentru a doua forma de impachetare	BB1
Numar unitati in a doua forma de impachetare	10
Inaltime a doua forma de impachetare	4,6 cm
Latime a doua forma de impachetare	13,6 cm
Lungime a doua forma de impachetare	33,4 cm
Greutate a doua forma de impachetare	308,0 g
Unitate de masura pentru a treia forma de impachetare	S02
Numar unitati in a treia forma de impachetare	40
Inaltime a treia forma de impachetare	15,0 cm
Latime a treia forma de impachetare	30,0 cm
Lungime a treia forma de impachetare	40,0 cm
Greutate a treia forma de impachetare	1,69 kg

Sustenabilitatea ofertei

Stare ofertă sustenabilă	Produs Green Premium
Regulamentul REACH	 Declaratia REACH
Conform REACH fara SVHC	Da
Directiva RoHS UE	Conform  Declaratia RoHS UE
Fara metale grele toxice	Da
Fara mercur	Da
Regulamentul RoHS China	 Declaratia RoHS China
Informatii privind scutirea de la RoHS	 Da
Raport de mediu	 Profilul Ambiental Al Produsului
Profil circularitate	Nu sunt necesare operatii de reciclare speciale
WEEE	În Uniunea Europeana, produsele trebuie reciclate respectand sistemul specific de colectare a deseurilor si nu trebuie sa ajunga in pubelele de colectare a deseurilor menajere.

Garanție contractuală

Garantie	18 months
----------	-----------