

# Product data sheet

## Characteristics

# ABL8BBU24200

battery control module - 24..28.8 V DC - 24 V - 20 A - for regulated SMPS



## Main

|                           |  |
|---------------------------|--|
| Range of product          | Phaseo   |
| Product or component type | Battery control module   |
| Input voltage             | 24...28.8 V DC   |
| Output voltage            | (U <sub>battery</sub> -0.5) V in battery mode DC<br>(U <sub>in</sub> -0.25) V in nominal mode DC |
| Maximum output current    | 20 A   |

## Complementary

|                                |  |
|--------------------------------|--|
| Input voltage limits           | 22...30 V  |
| Maximum power dissipation in W | 7 W  |
| Activation threshold           | Adjustable 22...36 V   |
| Number of output channels      | 1  |
| Current consumption            | 0.6 A on load<br>0.1 mA no load<br>≤ 40.6 A  |
| Output protection type         | Against overload, protection technology: 1.5 x I <sub>n</sub><br>Against short-circuits, protection technology: battery-backed mode, automatic reset<br>Against short-circuits, protection technology: power-supplied mode   |
| Connections - terminals        | For diagnostic relay: removable screw terminal block, connection capacity: 1 x 0.75 mm <sup>2</sup><br>For input connection: screw type terminals, connection capacity: 2 x 0.5...2 x 10 mm <sup>2</sup> AWG 20...AWG 8<br>For output connection: screw type terminals, connection capacity: 2 x 0.5...2 x 10 mm <sup>2</sup> AWG 20...AWG 8   |
| Fixing mode                    | By clips on 35 mm symmetrical DIN rail, operating position: horizontal<br>By clips on 35 mm symmetrical DIN rail, operating position: vertical   |
| Operating altitude             | 2000 m   |
| Marking                        | CE   |
| Name of test                   | Electrostatic discharges conforming to IEC 61000-4-2<br>Emission conforming to IEC 61000-6-3<br>Induced electromagnetic field conforming to IEC 61000-4-6 level 3<br>Radiated electromagnetic field conforming to IEC 61000-4-3 level 3<br>Rapid transient conforming to IEC 61000-4-4 level 3<br>Surge conforming to IEC 61000-4-5 level 2<br>Conducted/radiated emissions conforming to EN 55022 class B, 20 % |
| Local signalling               | 1 C/O relay for alarm status<br>1 C/O relay for battery status<br>1 C/O relay for power supply status<br>LCD screen for module status  |
| Width                          | 60 mm  |
| Height                         | 125 mm   |
| Depth                          | 160 mm   |
| Net weight                     | 0.5 kg   |

## Environment

|                                       |   |
|---------------------------------------|---|
| Product certifications                | RCM[RETURN]EAC  |
| Standards                             | UL 508<br>CSA C22.2 No 60950-1  |
| Ambient air temperature for operation | -25...60 °C   |
| Ambient air temperature for storage   | -40...85 °C   |
| Environmental characteristic          | EMC conforming to IEC 61000-6-3<br>EMC conforming to IEC 61000-6-2<br>Safety conforming to IEC 60950-1<br>Safety conforming to EN/IEC 61204-3 |
| IP degree of protection               | IP20 conforming to IEC 60529  |
| Dielectric strength                   | 500 V between input and ground<br>500 V between output and ground   |
| Overvoltage category                  | Class II conforming to VDE 0106-1   |
| Relative humidity                     | 0...90 % during operation<br>0...95 % during storage  |
| MTBF reliability                      | 718708 H at 24 V DC with UTE C80-810 calculation method   |
| Vibration resistance                  | 2 gn (f= 11.9...150 Hz) conforming to IEC 61131-2<br>3.5 mm (f= 3...11.9 Hz) conforming to IEC 61131-2  |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 9 cm      |
| Package 1 Width              | 19.5 cm   |
| Package 1 Length             | 19.5 cm   |
| Package 1 Weight             | 1.468 kg  |
| Unit Type of Package 2       | S03       |
| Number of Units in Package 2 | 8         |
| Package 2 Height             | 30 cm     |
| Package 2 Width              | 30 cm     |
| Package 2 Length             | 40 cm     |
| Package 2 Weight             | 11.929 kg |
| Unit Type of Package 3       | P06       |
| Number of Units in Package 3 | 72        |
| Package 3 Height             | 80 cm     |
| Package 3 Width              | 80 cm     |
| Package 3 Length             | 60 cm     |
| Package 3 Weight             | 118.7 kg  |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           |  <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  |
| Mercury free               | Yes   |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information |  <a href="#">Yes</a>                           |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a> |
| Circularity Profile        |  <a href="#">End Of Life Information</a>       |
| PVC free                   | Yes   |


## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## 24 Vdc/20 A Battery Control Module


### Dimensions

mm  
inch




24 Vdc Battery Control Module

Mounting




24 Vdc Battery Control Module

Clearance



## 24 Vdc Battery Control Module

### Wiring Diagram



(1) See table below for the maximum unstored charge capacity (μF)

| ABL       | Max. Unstored Charge Capacity (μF) |
|-----------|------------------------------------|
| 8RPS24030 | 30 000                             |
| 8RPS24050 | 50 000                             |
| 8RPS24100 | 100 000                            |
| 8RPM24200 | 100 000                            |
| 8WPS24200 | 100 000                            |
| 8WPS24400 | 100 000                            |

## 24 Vdc Battery Control Module

Outputs States (U = 24 Vdc: I > 5 mA, U = 230 Vac: I < 500 mA)

|  |                                |  |                             |
|--|--------------------------------|--|-----------------------------|
|  | No power from the power supply |  | Power from the power supply |
|  | Alarm or device not supplied   |  | No alarm                    |
|  | No power from the battery pack |  | Power from the battery pack |





### Inputs States (Dry Contact)

|  |                     |  |                   |
|--|---------------------|--|-------------------|
|  | Operational battery |  | Battery inhibited |
|--|---------------------|--|-------------------|





### Wiring Requirements

## Cable Types and Wire Sizes

IEC / EN

|   |                                |  |  |
|---|--------------------------------|--|--|
|  |                                | <b>ABL</b><br><b>8RPS24030</b><br><b>8RPS24050</b><br><b>8RPS24100</b> | <b>ABL</b><br><b>8RPM24200</b><br><b>8WPS24200</b><br><b>8WPS24400</b> |
| $\varnothing \leq 4 \text{ mm}^2$   | $\varnothing > 4 \text{ mm}^2$ |  |  |
| <b>ABL 8BBU24200</b>  | In + / -                       | 1... 4 mm <sup>2</sup>   | 4... 10 mm <sup>2</sup>  |
|   | ⏻ + / -                        | 6 mm <sup>2</sup>  | —  |
|   | Out + / -                      | 6 mm <sup>2</sup>  | —  |
| <b>ABL 8BBU24400</b>  | In + / -                       | 1... 4 mm <sup>2</sup>   | 4... 10 mm <sup>2</sup>  |
|   | ⏻ + / -                        | 10 mm <sup>2</sup>   | —  |
|   | Out + / -                      | 10 mm <sup>2</sup>   | —  |
|  |                                | 10 mm <sup>2</sup>   | —  |
|  |                                | —  | —  |
|  |                                | 0, 14... 1 mm <sup>2</sup>   | —  |

UL

|   |                                |  |  |
|---|--------------------------------|--|--|
|  |                                | <b>ABL</b><br><b>8RPS24030</b><br><b>8RPS24050</b><br><b>8RPS24100</b> | <b>ABL</b><br><b>8RPM24200</b><br><b>8WPS24200</b><br><b>8WPS24400</b> |
| $\varnothing \leq 12 \text{ AWG}$   | $\varnothing > 12 \text{ AWG}$ |  |  |
| <b>ABL 8BBU24200</b>  | In + / -                       | 16... 12 AWG   | 12... 6 AWG  |
|   | ⏻ + / -                        | 10 AWG   | —  |
|   | Out + / -                      | 10 AWG   | —  |
| <b>ABL 8BBU24400</b>  | In + / -                       | 16... 12 AWG   | 12... 6 AWG  |
|   | ⏻ + / -                        | 6 AWG  | —  |
|   | Out + / -                      | 6 AWG  | —  |
|  |                                | 6 AWG  | —  |
|  |                                | —  | —  |
|  |                                | 26... 16 AWG   | —  |