


Product data sheet

Characteristics

NSYEC761

Spacial SF 1 entry cable gland plate - fixed by clips - 700x600 mm



Main

Range	Spacial
Product or component type	Cable gland plate
Accessory / separate part category	Cable management accessory
Application	Prisma application Multi-purpose
Range compatibility	Spacial Spacial SF Spacial Spacial SFP
Mounting location	Enclosure bottom
Cable gland type	Standard
Cable entry	1 entry
Device composition	Fixing elements 1 plate Polyurethane adhesive gasket with cross-section of 15 x 25 mm
Quantity per set	Set of 1
Material	Galvanised steel

Complementary

Width	700 Mm nominal: 516 mm useful:
Depth	600 mm nominal:
Thickness	1.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	34.5 cm
Package 1 Length	55.0 cm
Package 1 Weight	3.898 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	40
Package 2 Height	45.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	169.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------