

# Product data sheet

## Characteristics

# NSYSF20350

Spacial SF enclosure without mounting plate - assembled - 2000x300x500 mm



### Main

Range	Spacial
Extended range	Spacial SF
Application	Multi-purpose Prisma application
Product or component type	Suitable enclosure
Enclosure nominal height	2000 mm
Enclosure nominal width	300 mm
Enclosure nominal depth	500 mm
Enclosure mounting	Floor-standing
Device composition	1 roof 1 structure 1 locking system with handle: door 1 door 1 rear panel

### Complementary

Structure type	Vertical uprights joined with top and bottom frames Perforated structure with a pitch of 25 mm Formed from a single section Panels and doors built into the structure
Door opening side	Reversible (120 °)
Door type	Plain front
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Lock type	4 points lock, handle with 5 mm double bar insert front door
Number of doors	Front: 1 door(s)
Accessibility for operation	Sides of enclosure Rear Front
Removable parts	Door by screws hinge Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws
Material	Frame: galvanised steel Uprights: galvanised steel Door: sheet steel Panels: sheet steel Hinge: zamak Handle: polyamide 6 with 30 % fibre glass
Surface finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)
Net weight	58 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Standards	IEC 62208
NEMA degree of protection	NEMA 3R/12
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	39.0 cm
Package 1 Width	55.0 cm
Package 1 Length	213.0 cm
Package 1 Weight	60.0 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	2
Package 2 Height	213.0 cm
Package 2 Width	55.0 cm
Package 2 Length	78.0 cm
Package 2 Weight	120.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------