

## Product data sheet

### Characteristics

# TCSECN300R2

ConneXium Ethernet copper cable for Ethernet network - 300 m



### Main

Range of product	ConneXium
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Product or component type	Ethernet copper cable
Accessory / separate part destination	Ethernet network
Cable length	300 m
Cable packaging	Roll

### Complementary

Transmission rate	100 Mbit/s 80 m
Transmission support medium	Double shielded twisted pair
AWG gauge	AWG 24
Marking	CE
Conductor material	Copper





### Environment

Standards	EN 50173 class D UL 508-CM EIA/TIA-568 category CAT 5E
-----------	--

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25.0 cm
Package 1 Width	37.0 cm
Package 1 Length	37.0 cm
Package 1 Weight	13.32 kg
Unit Type of Package 2	P12
Number of Units in Package 2	10
Package 2 Height	65.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	133.2 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------