



Product data sheet

Characteristics

GV2LC0220R

enclosed DOL starter TeSys - GV2-LC - 18 A

Main

Range of product	TeSys
Device short name	GV2LC
Motor starter type	Non reversing
Product or component type	Enclosed DOL starter
Poles description	3P
Motor starter composition	With circuit breaker
Trip unit technology	Magnetic
Thermal protection adjustment range	18 A
Control type	Rotary handle red
Enclosure material	Polycarbonate

Complementary

[Ue] rated operational voltage	690 V
Breaking capacity	10 kA Icu at 500 V conforming to IEC 60947-2 100 kA Icu at 220...230 V conforming to IEC 60947-2 20 kA Icu at 440 V conforming to IEC 60947-2 50 kA Icu at 400...415 V conforming to IEC 60947-2
Cable entry	2 x 20 mm ISO at top 2 x 20 mm ISO at bottom 2 x 25 mm ISO at top 2 x 25 mm ISO at bottom
Locking options description	1 to 3 padlocks Ø 8 Padlock in OFF position
Width	88 mm
Height	166 mm
Depth	173 mm
Net weight	0.78 kg

Environment

Standards	IEC 60439-1 IEC 60947-4 EN 60947 VDE 0660-102
IP degree of protection	IP547 conforming to IEC 60529

Contractual warranty

Warranty	18 months
----------	-----------