

Product data sheet

Characteristics

LAD703Q

TeSys D thermal overload relays - remote electrical stop - 380...400V AC



Main

Range	TeSys
Product or component type	Electrical remote stop
Device short name	LAD
Accessory / separate part category	Electrical accessory
Product compatibility	LR3D01...D35 LRD01...35 LR3D313...LR3D365 LRD313...LRD365
[Uc] control circuit voltage	380/400 V AC 50/60 Hz

Complementary

Maximum inrush power in VA	100 VA
Net weight	0.09 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.1 cm
Package 1 Width	4.9 cm
Package 1 Length	4.9 cm
Package 1 Weight	105.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	32
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.585 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------