

Product data sheet

Characteristics

LUA8E20

control power disconnect module



Main

Range	TeSys
Device short name	LUA8
Product or component type	Auxiliary contact

Complementary

Auxiliary contact composition	2 NO
Signalling function	Start-stop
[Ue] rated operational voltage	690 V AC 690 V DC
[Ith] conventional free air thermal current	5 A
Minimum switching voltage	17 V
Minimum switching current	80 mA
Net weight	0.048 kg
Connections - terminals	Screw clamp terminals

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	11.0 cm
Package 1 Length	8.8 cm
Package 1 Weight	60.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	50
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.36 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Contractual warranty	
Warranty	18 months