

Product data sheet

Characteristics

NSYCEA35W230VLE

ClimaSys Exchanger air-air35W/K later. without T



Main

Range	ClimaSys
Product name	ClimaSys CE
Product or component type	Air-air exchanger
Mounting type	Sides of enclosure
Cooling power	35 W power is obtained by multiplying specific power by DeltaT (Tex.t-Tint.)

Complementary

Flow rate	External circuit: 450 m3/h Internal circuit: 450 m3/h
Exchange surface	1.5 m ²
Nature of the fluid	Air
Input voltage	230 V 50/60 Hz
[In] rated current	0.7 A
Inrush current	2.1 A
Power consumption in W	150 W
Height	780 mm external:
Width	325 mm external:
Depth	144 mm external:
Net weight	15 kg
Noise level	64 dB
Colour	Grey (RAL 7035)
Condition of use	The enclosure must be at least IP54 Outside temperature must be 5 °C lower than inside temperature

Environment

IP degree of protection	IP22 (external IP) IP54 (internal IP)
-------------------------	--

Contractual warranty

Warranty	18 months
----------	-----------