

Product data sheet

Characteristics

NSYCEW3150W230VL

ClimaSys Exchanger air-water 3150W lateral



Main

Range	ClimaSys
Product name	ClimaSys CE
Product or component type	Air-water exchanger
Mounting type	Sides of enclosure
Cooling power	3150 W

Complementary

Pressure	1 MPa for water
Flow rate	External circuit: 820 m3/h
Control type	Thermostat
Temperature setting range	8...50 °C
Controlled fluid	Water
Input voltage	230 V 50/60 Hz
[In] rated current	1.7 A
Inrush current	1.3 A
Output type	Inverter contact
Height	950 mm external:
Width	400 mm external:
Depth	190 mm external:
Net weight	21 kg
Noise level	54 dB
Material	Steel
Colour	Grey (RAL 7035)
Condition of use	The enclosure must be at least IP54 Outside temperature could be higher than inside temperature

Environment

IP degree of protection	IP55 conforming to DIN 40050
Product certifications	UL

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	95 cm
Package 1 Width	40 cm
Package 1 Length	19 cm
Package 1 Weight	21 kg

Contractual warranty

Warranty	18 months
----------	-----------