


Product data sheet

Characteristics

NSYCRS100W120V

Climasys Ultra thin resistance heater low starting current 90W 120V 280x450mm



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Ultra thin resistance heater
Power range	90 W
Input voltage	120 V AC 50/60 Hz
Electrical connection	Cable length: 2 m

Complementary

Operating position	Vertical Horizontal
Ambient air temperature for operation	-60...70 °C
Temperature setting range	-40...70 °C
Material	Silicone rubber
Height	260 mm external:
Width	440 mm external:
Depth	1.6 mm external:
Device composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts Fixing accessories
Condition of use	Heaters must be installed with a thermal controller Electrical protection is needed Air sealed enclosure
Fixing mode	By 4 screws
Mounting support	Telequick mounting plate Adhesive Velcro Standard mounting plate DIN rail

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------