

Product data sheet

Characteristics

NSYTVR12

Set of 2 heavy duty vertical rails for fixing of chassis and cross rails-1200 mm



Main

Range	Spacial
Accessory / separate part category	Mounting accessory
Product or component type	Technical upright
Device application	Multi-purpose
Enclosure nominal dimensions	- H: 1200 mm
Mounting support	Mounting plate fixing bracket Upright fixing bracket
Range compatibility	Spacial Spacial SF Spacial Spacial SM
Device composition	2 upright
Quantity per set	Set of 1
Material	Steel

Complementary

Surface finish	Zinc coated
Adjustment	Adjustable in depth every 25 mm with caged nuts Adjustable in height every 2.5 mm with quarter-turn nuts
Height	1200 Mm Real: 1075 mm
Width	45 mm
Depth	34 mm
Thickness	2 mm
Cut-out dimensions	13 x 11 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.0 cm
Package 1 Length	108.0 cm
Package 1 Weight	3.24 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	100
Package 2 Height	50.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	337.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Logistical informations

Country of origin	FR
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------