

# Product data sheet

## Characteristics

# VW3A3616

## Ethernet TCP/IP communication module



### Main

|                                    |                           |
|------------------------------------|---------------------------|
| Range of product                   | Altivar                   |
| Product or component type          | Communication module      |
| Accessory / separate part category | Communication accessories |






### Complementary

|                             |  |
|-----------------------------|--|
| Product compatibility       | Lexium 32M   |
| Range compatibility         | Altivar Machine ATV320<br>Altivar 32<br>Lexium 32  |
| Communication port protocol | Modbus TCP<br>EtherNet/IP  |
| Electrical connection       | 1 connector RJ45, EtherNet/IP<br>1 connector RJ45, Modbus TCP  |
| Transmission rate           | 10/100 Mbps  |
| Addressing                  | IP addressing manual, BOOTP or DHCP  |
| Exchange mode               | Half duplex and full duplex  |
| Communication service       | Up to 8 connections (includes connections of Modbus TCP/Ethernet IP) for Ethernet IP/Modbus TCP<br>FDR Agent for Ethernet IP/Modbus TCP<br>Read holding registers (03), 63 words max for Modbus TCP<br>Read input registers (04), 63 words max for Modbus TCP<br>Write single register (06) for Modbus TCP<br>Write multiple registers (16), 63 words max for Modbus TCP<br>Read/Write multiple registers (23) for Modbus TCP<br>Read device identification (43) for Modbus TCP<br>Diagnostics (08) for Modbus TCP<br>I/O scanner : read/write, 6 words maximum for Modbus TCP<br>Communication monitoring for Modbus TCP<br>SNMP agent for Ethernet IP<br>Master/Slave hierarchy ODVA AC drive profile and CiA 402 profile for Ethernet IP<br>Fixed communication monitoring adjusted by Ethernet IP scanner adaptor (Master) for Ethernet IP |
| Display type                | 1 LED for MS (Module Status)<br>1 LED for NS (Network Status)<br>1 LED for Ethernet port activity<br>1 LED for Modbus TCP port activity  |
| Net weight                  | 0.3 kg   |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 4.200 cm  |
| Package 1 Width              | 6.100 cm  |
| Package 1 Length             | 9.000 cm  |
| Package 1 Weight             | 60.000 g  |
| Unit Type of Package 2       | S03       |
| Number of Units in Package 2 | 100       |
| Package 2 Height             | 30.000 cm |
| Package 2 Width              | 30.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 6.590 kg  |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| REACH Regulation           |  <a href="#">REACH Declaration</a>  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>   |
| RoHS exemption information |  <a href="#">Yes</a>   |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a>  |
| Circularity Profile        | No need of specific recycling operations   |
| PVC free                   | Yes  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|