

Product data sheet

Characteristics

XAWF110EX

Control station, metal, stop function, 1 flush push button, red, 1 NC, ATEX



Main

| | |
|-----------------------------|--|
| Range of product | Harmony XAW |
| Product or component type | Complete control station |
| Device short name | XAWF |
| Control station application | Stop function |
| Material | Metal |
| Control station composition | 1 flush push-button, red, spring return 1 NC |

Complementary

| | |
|--------------------------------|--|
| Colour of base of enclosure | Black |
| Colour of cover | Black |
| Cable entry | 1 entry for ISO M20 cable gland |
| Width | 80 mm |
| Depth | 77 mm |
| Height | 80 mm |
| Net weight | 0.830 kg |
| Marking | Ex tb IIIC T85°C Db IP65 |
| Mechanical durability | 5000000 cycles |
| Short-circuit protection | 10 A cartridge fuse type gG |
| [Ie] rated operational current | 3 A at 240 V, AC-15, A600 conforming to EN/IEC 60947-5-1 6 A at 120 V, AC-15, A600 conforming to EN/IEC 60947-5-1 0.1 A at 600 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 0.27 A at 250 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 0.55 A at 125 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 1.2 A at 600 V, AC-15, A600 conforming to EN/IEC 60947-5-1 |

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for operation | -20...60 °C |
| Overvoltage category | I conforming to IEC 60536 |
| IP degree of protection | IP65 conforming to IEC 60529 |
| Standards | EN 60079-0:2009 EN 60079-31:2009 EN 60947-5-4 EN 61000-6-2 EN/IEC 60947-1 EN/IEC 60947-5-1 IEC 60079-0:2007 IEC 60079-31:2008 |
| Directives | 94/9/EC - ATEX directive |
| Dust zone | Zone 21 - 22 |
| Product certifications | INERIS 04ATEX0023X |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|