

# Product data sheet

## Characteristics

# XPSATE5110

module XPSAT - Emergency stop - 24 V AC/DC



## Main

Range of product	Preventa Safety automation
Product or component type	Preventa safety module
Safety module name	XPSATE
Safety module application	For emergency stop and switch monitoring
Function of module	Emergency stop button with 2 NC contacts
Safety level	Can reach PL d/category 3 time delay safety outputs conforming to EN/ISO 13849-1 Can reach PL e/category 4 instantaneous safety outputs conforming to EN/ISO 13849-1 Can reach SILCL 3 instantaneous safety outputs conforming to EN/IEC 62061 Can reach SILCL 2 time delay safety outputs conforming to EN/IEC 62061
Safety reliability data	DC > 99 % conforming to EN/ISO 13849-1 instantaneous safety outputs MTTFd = 134.8 years conforming to EN/ISO 13849-1 instantaneous safety outputs MTTFd = 54.5 years conforming to EN/ISO 13849-1 time delay safety outputs DC > 98.4 conforming to EN/ISO 13849-1 time delay safety outputs PFHd = 6.81E-9 1/h conforming to EN/IEC 62061 instantaneous safety outputs PFHd = 1.96E-8 1/h conforming to EN/IEC 62061 time delay safety outputs
Type of start	Configurable
Connections - terminals	Captive screw clamp terminals, 1 x 0.14...1 x 2.5 mm <sup>2</sup> flexible with cable end, with double bezel Captive screw clamp terminals, 1 x 0.14...1 x 2.5 mm <sup>2</sup> solid with cable end, with double bezel Captive screw clamp terminals, 1 x 0.25...1 x 1.5 mm <sup>2</sup> flexible with cable end, with double bezel Captive screw clamp terminals, 1 x 0.25...1 x 2.5 mm <sup>2</sup> flexible with cable end, with double bezel Captive screw clamp terminals, 2 x 0.14...2 x 0.75 mm <sup>2</sup> flexible with cable end, with double bezel Captive screw clamp terminals, 2 x 0.14...2 x 0.75 mm <sup>2</sup> solid with cable end, with double bezel Captive screw clamp terminals, 2 x 0.25...2 x 1 mm <sup>2</sup> flexible with cable end, with double bezel Captive screw clamp terminals, 2 x 0.5...2 x 1.5 mm <sup>2</sup> flexible with cable end, with double bezel
Output type	Relay instantaneous opening, 2 NO circuit(s), volt-free Relay time delay opening, 3 NO circuit(s), volt-free
Number of additional circuits	3 solid state outputs
[Us] rated supply voltage	24 V AC/DC - 15...10 %

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company mentioned herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Complementary

Synchronisation time between inputs	75 ms
Supply frequency	50/60 Hz
Maximum power consumption in W	8 W
Input protection type	Internal, electronic
Time delay range	0...30 s
[Uc] control circuit voltage	24 V AC/DC
Breaking capacity	180 VA holding AC-15 C300 relay output 1800 VA inrush AC-15 C300 relay output
Breaking capacity	1 A at 24 V (DC-13) time constant: 50 ms for relay output
Output thermal current	2.5 A for time delay outputs 5 A for instantaneous outputs
[Ith] conventional free air thermal current	8 A
Associated fuse rating	4 A gG for time delay outputs conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200 6 A gG for instantaneous outputs conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200
Minimum output current	10 mA for relay output
Minimum output voltage	17 V for relay output
Maximum response time on input open	20 ms
[Ui] rated insulation voltage	300 V (pollution degree 2) conforming to IEC 60947-5-1 300 V (pollution degree 2) conforming to DIN VDE 0110 part 1
[Uimp] rated impulse withstand voltage	4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 part 1
Local signalling	4 LEDs
Mounting support	35 mm symmetrical DIN rail
Net weight	0.28 kg





## Environment

Standards	EN/IEC 60947-5-1 EN/IEC 60204-1 EN/ISO 13850
Product certifications	UL[RETURN]CSA[RETURN]TÜV
IP degree of protection	IP20 (terminals) conforming to EN/IEC 60529 IP40 (enclosure) conforming to EN/IEC 60529
Ambient air temperature for operation	-10...55 °C
Ambient air temperature for storage	-25...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.5 cm
Package 1 Width	6.2 cm
Package 1 Length	10.5 cm
Package 1 Weight	339.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	1
Package 2 Height	12.5 cm
Package 2 Width	6.2 cm
Package 2 Length	10.5 cm
Package 2 Weight	334.0 g
Unit Type of Package 3	S02
Number of Units in Package 3	12
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	4.647 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	<a href="#"> End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------

---

Dimensions

---

