


Product data sheet

Characteristics

XGSZ12E1210

OsiSense XG cable M12/M12 D coded - Ethernet - 10m



Main

Range of product	Telemecanique Radio frequency identification XG
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Product or component type	Ethernet copper cable
Product compatibility	XGSZ33EIP XGSZ33ETH
Accessory / separate part destination	Ethernet network

Complementary

Cable length	10 m
Transmission rate	100 Mbit/s
Transmission support medium	2 twisted shielded pairs
Communication network category	5e
AWG gauge	AWG 26
Electrical connection	1 male connector, M12 straight connector with 4 pin(s) - encoding type: D coding 1 male connector, M12 straight connector with 4 pin(s)
Conductor material	Copper
Cover material	PUR
Net weight	0.43 kg

Environment

IP degree of protection	IP67
Standards	IEC 60754-1 ISO/IEC 11801 Ed.2, 2002 EIA/TIA-568

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	28.000 cm
Package 1 Length	30.000 cm
Package 1 Weight	451.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	4
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.138 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------

Wiring Diagram

