

Product data sheet

Characteristics

XGSZ33EIP

Connection box EtherNet/IP - 3 channels for XGCS smart antennas



Main

Range of product	Telemecanique Radio frequency identification XG
Product or component type	Connection Ethernet IP box
Device short name	XGSZ33
Number of channels	3
Communication port protocol	EtherNet/IP
Associated smart antenna	XGCS89 XGCS49
Electrical connection	1 male connector M12 4 pins for power supply (A coding) 3 female connectors M12 5 pins for stations XGCS (A coding) 1 female connector M12 4 pins for Ethernet network (D coding)
[Us] rated supply voltage	24 V DC conforming to Protective Extra Low Voltage

Complementary

Supply voltage limits	21.6...26.4 V DC
Power consumption in W	2.5 W
Status LED	Module Status: 2 dual color LED (red/green) Network status: 3 dual color LED (red/green) Link: 1 LED (green) Activity: 1 dual color LED (red/green) Subnet status: 0 dual color LED (red/green) Device status: 1 dual color LED (red/green)
Communication service	Cyclical variable exchange
Register words	1...123 words
Transmission support medium	Ethernet cable
Transmission rate	10/100 Mbit/s
Marking	CE
Net weight	1.06 kg

Environment


Ambient air temperature for operation	0...55 °C
Ambient air temperature for storage	-25...85 °C
Relative humidity	30...95 %
IP degree of protection	IP65
EMC filter	Class B EMC filter conforming to EN 55022

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	16.2 cm
Package 1 Length	24.0 cm
Package 1 Weight	960.0 g

Unit Type of Package 2	S03
Number of Units in Package 2	3
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.43 kg

Offer Sustainability


REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions

Connection Boxes



Wiring Diagram

Ethernet Connections

Socket to Smart Antenna Cabling




Pin no.	Signal
1	Earth
2	+ 24 VDC
3	0 V
4	D0
5	D1

Socket to Power Supply Cabling




Pin no.	Signal
1	+ 24 VDC
2	+ 24 VDC
3	0 VDC
4	0 VDC

Socket to Ethernet connection



Socket to Ethernet cabling (M12 connectors)



Pin no.	Signal
1	TD+
2	TD-
3	RD+
4	RD-