


## Product data sheet

### Characteristics

# XMLEZ600

local display - for electronic pressure sensor  
600 bar



### Main

Accessory / separate part type	Display
Display type	Digital display
Operating position	Any position
Product compatibility	XMLE analogue pressure sensors 0...600 bar, connector type: EN 175301-803-A (ex DIN43650) XMLP analogue pressure sensors, connector type: EN 175301-803-A (ex DIN43650)

### Complementary

Net weight	0.1 kg
Height	66 mm
Depth	40 mm
Width	92 mm



### Environment

Vibration resistance	35 gn (f = 60...2000 Hz) 5 gn (f = 25...200 Hz)
Ambient air temperature for operation	-15...80 °C
Standards	CE
Product certifications	UL[RETURN]CSA

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	11.5 cm
Package 1 Length	9 cm
Package 1 Weight	122 g


### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

### Contractual warranty

Warranty	18 months
----------	-----------

Dimensions



(1)  $a = 75$