

Product data sheet

Characteristics

XVLA244

LED pilot light with integral lens cap, Harmony XVL, Ø 8, IP40/IP65, red, covered included, 48 V, faston



Main

Range of product	Harmony XVL
Product or component type	LED pilot light with integral lens cap
Component name	XVL
Mounting diameter	8 mm
Light source	Covered LED
Light block colour	Red
Protection type	Built-in by diode Integral ballast resistor
[Us] rated supply voltage	48 V
IP degree of protection	IP65 (with seal XVLZ911) conforming to IEC 60529 IP65 (with seal XVLZ911) conforming to NF C 20-010 IP40 conforming to IEC 60529 IP40 conforming to NF C 20-010

Complementary

Supply circuit type	DC
Connections - terminals	Tag for Faston connectors: 2.8 x 0.5 mm Tag for soldering connectors
Current consumption	10 mA
[Ui] rated insulation voltage	50 V conforming to IEC 60947-1
Bulb lifespan	100000 h
Nominal voltage limit	0.8...1.1 Un
Terminals description ISO n°1	(X1-X2)PL
Height	10 mm
Width	10 mm
Depth	36 mm
Net weight	0.003 kg

Environment

Product certifications	UL[RETURN]CSA
Protective treatment	TC
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Overvoltage category	Class 3 conforming to IEC 60536 Class 3 conforming to NF C 20-030

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.700 cm
Package 1 Width	4.500 cm
Package 1 Length	5.300 cm
Package 1 Weight	2.500 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	3.000 cm
Package 2 Width	12.000 cm
Package 2 Length	16.000 cm
Package 2 Weight	31.000 g
Unit Type of Package 3	S01
Number of Units in Package 3	100
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	535.000 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins


Logistical informations

Country of origin	FR
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------


Dimensions



C		Ø	
mm	in.	mm	in.
34	1.34	10	0.39

LED Pilot Light

Panel Drilling



Ø min		G min		H min	
mm	in.	mm	in.	mm	in.
8.2	0.32	10.5	0.41	10.5	0.41