



Overview

Presentation	Hocheffiziente dreiphasige USV mit internen Batterien. Die USV bietet modernste Funktionen, herausragende Spezifikationen und robuste Elektrik – für maximale Geschäftskontinuität im Datacenter oder Technikraum. Diese USV mit 15 kVA lässt sich leicht installieren, bedienen und warten. Sie eignet sich ideal für kleine und mittlere Unternehmen. Das System enthält Staubfilter und speziell beschichtete Leiterplatten für anspruchsvolle Raumbedingungen.
Lead time	Usually Ships within 6 Weeks

Main

Main Input Voltage	400 V 3 phases
Product or component type	Uninterruptible power supply (UPS)
Other Input Voltage	380 V 415 V
Main Output Voltage	400 V 3 phases
Other Output Voltage	380 V 415 V
Rated power in W	15 kW
Rated power in VA	15 kVA
Provided equipment	Dust filter Installation guide

Batteries & Runtime

Battery type	VRLA
Battery voltage	240 V
Maximum short-circuit current	10 kA
Number of battery filled slots	1
Number of battery free slots	2

Physical

Colour	White (RAL 9003)
Height	140 cm
Width	38 cm
Depth	92.8 cm
Net weight	436 kg
USB compatible	Yes

Input

Maximum input current	28 A
Input harmonic distortion	Less than 3 % for full load
Load power factor	0.9 leading to 0.9 lagging
Input Power Factor at Full Load	0.99
Input voltage limits	304...477 V
Network frequency	45...65 Hz

Output

Maximum configurable power in VA	15 kVA
Maximum configurable power in W	15 kW
Output frequency	50 Hz sync to mains 60 Hz sync to mains
Harmonic distortion	Less than 3 %
Output harmonic distortion	< 3% linear load
Output voltage tolerance	+/- 1.5 %
UPS type	Double conversion online
Additional information	UPS weight does not include battery weight.

Conformance

Product certifications	CE[RETURN]EAC[RETURN]RCM
------------------------	--------------------------

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3333 ft
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0.00...15240.00 m
Acoustic level	60 dBA
Heat dissipation	852 W
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	164 cm
Package 1 Width	101.4 cm
Package 1 Length	56.3 cm
Package 1 Weight	481 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	Ein Jahr Vor-Ort-Reparatur oder Austausch mit werkseitig autorisierter Inbetriebnahme
----------	---