



Main

Range	Exiway
Product name	Exiway One
Product or component type	Emergency luminaire
Device application	Anti-panic lighting
Function	Standard Self-test
Operational mode	Non-maintained
Number of batteries	1 x 6 V 1.5 Ah Ni-Cd (Nickel-Cadmium)
Colour tint	White
Light source	Fluorescent tube G5 8 W LED 8 W
Light source colour	White
Cover type	Transparent
Wiring device additional information	Can be inhibited with rest mode via Teleur range of remote controls

Complementary

Mounting support	Ceiling False ceiling Wall
[Ue] rated operational voltage	220...230 V AC/DC 50 Hz
Power consumption in VA	4.1 VA
Power consumption in W	2.7 W 2.6 W
Current consumption	17 mA
Electrical insulation class	Class II
Autonomy	1 h
Charging time	12 h
Type of glass	Fresnel glass
Material	Housing: plastic Cover: plastic
Height	160 mm
Depth	68 mm
Width	375 mm

Environment

IP degree of protection	IP65
IK degree of protection	IK07
Fire resistance	850 °C
Product certifications	AENOR[RETURN]ENEC
Ambient air temperature for operation	0...40 °C
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.4 cm
Package 1 Width	8 cm
Package 1 Length	38.1 cm
Package 1 Weight	1.23 kg

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------