



Main

Range	Exiway
Product name	Exiway One
Product or component type	Emergency light fitting
Device application	Lighting
Function	Standard Self-test
Supply	Non-maintained
Number of batteries	1 x 6 V 1.5 Ah Ni-Cd (Nickel-Cadmium)
Colour	White
Light source	Fluorescent tube G5 8 W LED 8 W
Light source colour	White
Cover type	Transparent
Wiring device additional information	Can be inhibited with rest mode via Teleur range of remote controls

Complementary

Range compatibility	Remote control
[Ue] rated operational voltage	220...230 V AC/DC 50 Hz
Power consumption in VA	4.1 VA
Power consumption in W	2.7 W 2.6 W
Current consumption	17 mA
Electrical insulation class	Class II
Autonomy	1 h
Charging time	12 h
Type of glass	Fresnel glass
Material	Housing: plastic Cover: plastic
Device mounting	Surface ceiling Hanging ceiling Flush false ceiling Flush wall Surface wall Electrified track
Height	160 mm
Width	375 mm
Depth	68 mm

Environment

IP degree of protection	IP65
IK degree of protection	IK07
Ambient air temperature for operation	0...40 °C
Fire resistance	850 °C
Product certifications	AENOR ENEC
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.23 kg
Package 1 Height	16.4 cm
Package 1 width	8 cm
Package 1 Length	38.1 cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------