

SRT8KXLI

APC Smart-UPS On-Line, 8kVA/8kW, Tower,
230V 3:1 and 1:1, 6x C13+4x C19 IEC outlets,
Network Card+SmartSlot, Extended runtime,
W/O rail kit



Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V 400 V 3 phases
Product or component type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V 380 V 415 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	8000 W
Rated power in VA	8000 VA
Output connection type	6 IEC 60320 C13 3 IEC Jumpers 4 IEC 60320 C19
Output connector type	Hard wire 3-wire (H N + E) 1
Provided equipment	CD with software Documentation CD Installation guide Temperature probe USB cable Warranty card Web/SNMP management card

Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Battery recharge time	1.5 h
Number of battery replacement quantity	2
Battery voltage	+/- 192 V (split battery referenced to neutral)
Battery charger power	876 W rated
Battery life	3...5 year(s)
Extended runtime	1

General

UPS type	Double conversion online
Product web sub-family	High density
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Colour	Black
Height	43.2 cm
Width	26.3 cm
Depth	71.5 cm
Net weight	111.82 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes

Input

Network frequency	40...70 Hz auto-sensing
Number of input connectors	1 hard wire 3-wire (1P + N + E) 1 hard wire 5-wire (3P + N + E)
Input voltage limits	100...275 V adjustable (half load) 173...476 V adjustable (half load)

Output

Maximum configurable power in VA	8000 VA
Maximum configurable power in W	8000 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Wave type	Sine wave
Harmonic distortion	Less than 2 %
Crest factor	3 : 1
Bypass type	Internal bypass (automatic and manual)

Conformance

Product certifications	CE[RETURN]EAC[RETURN]IRAM[RETURN]RCM[RETURN]VDE
Marking	CE Mark
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0.00...15240.00 m
Acoustic level	55 dBA
Heat dissipation	1497 Btu/h
IP degree of protection	IP20

Communications & Management

Free slots	1
Preinstalled device	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity
Emergency power off	Yes






Surge Protection and Filtering

Surge energy rate	480 J
-------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	46.1 cm
Package 1 Width	60 cm
Package 1 Length	100 cm
Package 1 Weight	126.82 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---