

Tehničke karakteristike proizvoda

Karakteristike

MUR37914

Mureva Styl - nadgradna kutija - dvostruka
horizontalna - siva



Osnovne informacije

Grupa proizvoda	Mureva Styl
Tip proizvoda ili komponente	Montažna kutija
Kompatibilnost grupe proizvoda	Mureva Styl orman
Nijansa boje	Siva (RAL 7016)

Dopunske informacije

Montaža uređaja	Nadgradno
Broj grupa	Dvostruki horizontalno
Kablovski uvod	Jednostavan pristup ventilu
Uslovi upotrebe	U zatvorenom/na otvorenom
Materijal	SEBS PP (polipropilen)
Udaljenost između centara	71 mm
Dužina	147 mm
Visina	54 mm
Širina	76 mm
Dubina	54 mm
Chemical and detergent products resistance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

Okruženje

Oznake kvaliteta	AENOR NF
Ip stepen zaštite	IP55
Ik stepen zaštite	IK08
Otpornost na plamen	Samogasivo 650 °C conforming to IEC 60695-2-1
Temperatura okoline za rad uređaja	-5...40 °C
Temperatura okoline za skladištenje	-25...55 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,400 cm
Package 1 Width	7,600 cm
Package 1 Length	14,700 cm
Package 1 Weight	124,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	8,000 cm
Package 2 Width	16,000 cm
Package 2 Length	39,500 cm
Package 2 Weight	715,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	30
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	5,022 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
Sustainable packaging	Yes
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja