

Tehničke karakteristike proizvoda

Karakteristike

WDE000514

Cedar Plus - jednopolni prekidač - 16AX, lokatorska lampica, beli



Osnovne informacije

Range name	Cedar Plus
Tip proizvoda ili komponente	Prekidač sa signalnom lampicom
Function	Jednopolni
Delivery form	Kompletan proizvod
Signalna lampica	Lokatorska lampica
Cover plate color	Bela

Dopunske informacije

Installation	Nadgradno
Opseg snage	3680 W
Nazivna struja	16 AX pri 250 V AC
Kind of terminals	Vijčani priključci
Terminal capacity	2 kabl(ovi) 2,5 mm ²
Wire structure	Kruti Fleksibilni
Dužina ogoljenog dela žice	11 mm
Material of visible parts	PA6 FR850
Završna obrada	Sjajno
Visina	79 mm
Širina	66 mm
Dubina	48 mm
Masa proizvoda	0,097 kg

Okruženje

Sertifikacija proizvoda	KEMA
Ip stepen zaštite	IP44

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,800 cm
Package 1 Width	6,600 cm
Package 1 Length	7,900 cm
Package 1 Weight	97,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	18,500 cm
Package 2 Width	9,000 cm

Package 2 Length	27,000 cm
Package 2 Weight	1,115 kg
Unit Type of Package 3	S03
Number of Units in Package 3	60
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	7,218 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
REACh bez SVHC	Da
EU RoHS direktiva	У складу са изузецима
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------