

AR3150SP

APC NetShelter SX, Server Rack Enclosure,
42U, Shock Packaging, 2000 lbs, Black, 2124H
x 750W x 1070D mm



Overview

Presentation	NetShelter SX Gehäuse und Verpackungssystem, schützt integrierte IT-Systeme mit bis zu 907 kg bei Transport, Verladung und Implementierung. Das Gehäuse ist mit einer stoßdämpfenden Palette, Verloaderampe und stoßfesten Hülle kombiniert. Das System wurde entwickelt und getestet für den sicheren Versand von vollständig konvergenten, vorbestückten Racks wie sie z. B. für Cisco® und den Versand des Cisco Unified Computing System (UCS) zertifiziert sind.
Lead time	Usually in Stock

Main

Product or component type	Rack enclosure
Number of rack unit	42U
Provided equipment	Baying hardware Documentation CD Key(S) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels

Physical

Height	199.1 cm
Width	75 cm
Depth	107 cm
Net weight	155.96 kg
Colour	Black
Mounting preference	No preference
Mounting mode	Not rack-mountable
Maximum mounting depth	91.49 cm
Minimum mounting depth	26.19 cm
Rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	1020.58 Kg dynamic 1700.97 kg static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	217.9 cm
Package 1 Width	132.1 cm
Package 1 Length	110.5 cm
Package 1 Weight	271.25 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Take-back	Take-back program available

Contractual warranty

Warranty	5 Jahre Reparatur oder Austausch
----------	----------------------------------