



### Main

Range	PowerLogic
Product name	PowerLogic PM3000
Device short name	PM3200
Product or component type	Power meter

### Complementary

Power quality analysis	Up to the 15th harmonic
Device application	Multi-tariff Sub billing Power monitoring
Type of measurement	Active and reactive power Apparent power Current Voltage Energy Power factor Frequency
Supply voltage	100...277 V AC 45...65 Hz 173...480 V AC 45...65 Hz 100...300 V DC
Network frequency	50 Hz 60 Hz
[In] rated current	5 A 1 A
Type of network	3P + N 3P 1P + N
Power consumption in VA	5 VA
Display type	Backlit LCD
Display resolution	128 x 96 pixels
Sampling rate	32 samples/cycle
Measurement current	0.05...6 A 0.02...1.2 A
Analogue input type	Current 0...5 A Current 0...1 A
Measurement voltage	50...330 V AC 45...65 Hz direct 50...330 V AC 45...65 Hz phase to neutral 80...570 V AC 45...65 Hz direct 80...570 V AC 45...65 Hz phase to phase 570...999000 V AC 45...65 Hz with external VT
Frequency measurement range	45...65 Hz
Number of inputs	0
Measurement accuracy	Current 0.3 % 0.5...6 A Current 0.5 % 0.1...1.2 A Voltage 0.3 % 50...330 V Voltage 0.3 % 80...570 V

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Accuracy class	Class 0.5S active energy conforming to IEC 62053-22 Class 1 active energy conforming to IEC 62053-21 Class 2 reactive energy conforming to IEC 62053-23 Class C active energy conforming to EN 50470-3
Number of outputs	0
Information displayed	Tariff (4)
Communication port protocol	-
Communication port support	-
Data recording	Min/max of instantaneous values
Mounting mode	Clip-on
Mounting support	DIN rail
Standards	BS EN 61557-12 IEC 61557-12 EN 61557-12 BS EN 61326-1 IEC 61326-1 EN 61326-1 BS EN 62052-11 IEC 62052-11 EN 62052-11 BS EN 62053-21 IEC 62053-21 EN 62053-21 BS EN 62053-22 IEC 62053-22 EN 62052-22 BS EN 62053-23 IEC 62053-23 EN 62052-23 BS EN 61010-1 EN 61010-1 IEC 61010-1 UL 61010-1 BS EN 61010-2-30 IEC 61010-2-30 EN 61010-2-30 UL 61010-2-30 ANSI C12.20
Product certifications	CE conforming to IEC 61010-1 (safety) CE conforming to EN 61557-12 (power monitor) CE conforming to EN/IEC 61326-1 (EMC) UKCA conforming to BS EN 61010-1 (safety) UKCA conforming to BS EN 61557-12 (power monitor) UKCA conforming to BS EN 61326-1 (EMC) CULus conforming to EN 61010-1 (safety) CULus conforming to UL 61010-1 (safety) EAC (sub-meter) RCM
Width	90 mm
Depth	70 mm
Height	95 mm
Net weight	0.26 kg

## Environment

Electromagnetic compatibility	Electrostatic discharge level 4 conforming to IEC 61000-4-2 Susceptibility to electromagnetic fields level 3 conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test level 4 conforming to IEC 61000-4-4 Surge immunity test level 4 conforming to IEC 61000-4-5 Conducted RF disturbances level 3 conforming to IEC 61000-4-6 Magnetic field at power frequency - test level: 0.5 mT conforming to IEC 61000-4-8 Conducted and radiated emissions class B conforming to EN 55022
Overvoltage category	III
IP degree of protection	IP40 front panel: conforming to IEC 60529 IP20 body: conforming to IEC 60529
Relative humidity	5...95 % at 50 °C
Pollution degree	2
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Operating altitude	< 3000 m

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.8 cm
Package 1 Width	13.2 cm
Package 1 Length	13.7 cm
Package 1 Weight	384 g
Unit Type of Package 2	S03
Number of Units in Package 2	16
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	6.567 kg
Unit Type of Package 3	P12
Number of Units in Package 3	128
Package 3 Height	15 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	57.672 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------