



Main

Range	Resi9
Product name	Resi9 MCB
Product or component type	Miniature circuit-breaker
Device application	Distribution
Poles description	3P
Number of protected poles	3
[In] rated current	10 A at 30 °C
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	3000 A Icn at 400 V AC 50/60 Hz conforming to EN/IEC 60898-1
Standards	EN/IEC 60898-1
Product certifications	CEBEC

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	400 V AC 50/60 Hz
Magnetic tripping limit	5...10 x In
Limitation class	3 conforming to EN/IEC 60898-1
[Ui] rated insulation voltage	440 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	4 kV
Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Bottom: biconnect
9 mm pitches	6
Height	85 mm
Width	54 mm
Depth	75 mm
Embedding depth	44 mm
Net weight	0.321 kg
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles AC 50/60 Hz conforming to EN/IEC 60898-1
Locking options description	Padlock in OFF position
Connections - terminals	Tunnel type terminals (bottom) - <= 16 mm² - flexible Tunnel type terminals (bottom) - <= 25 mm² - rigid Tunnel type terminals (top) - <= 25 mm² - rigid Tunnel type terminals (top) - <= 16 mm² - flexible
Tightening torque	2 N.m

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.





Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	2 conforming to EN/IEC 60898-1
Overvoltage category	III
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	6.6 cm
Package 1 Length	8.0 cm
Package 1 Weight	310.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	8.5 cm
Package 2 Width	9.0 cm
Package 2 Length	22.5 cm
Package 2 Weight	1.334 kg
Unit Type of Package 3	S03
Number of Units in Package 3	48
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	16.495 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product
Minimum percentage of recycled plastic content	56

Contractual warranty

Warranty	18 months
----------	-----------