



Main

Range of product	TwinBus
Product or component type	Comfort handsfree video intercom unit
Control button type	Control keys to move in menu structure Door opener button Light switch button Privacy button Voice connection button
Colour tint	White
Intercom type	Hand-held operation

Complementary

Mounting mode	Surface mounted Desktop installation
Display type	Backlight colour TFT
Display resolution	320 x 240 pixels
Display size	3.5 inch
Brightness	Adjustable
Contrast	Adjustable
Information displayed	Menu-driven operation interface in 13 languages
Material	ABS (acrylonitrile butadiene-styrene)
Supply	Via TwinBus power supply unit video
Function available	Call tone differentiation for door/floor/internal call Optical call display Call interface relay 1 configurable button Voice volume control Call memory
Connections - terminals	Audio and video bus
Signalling type	20 adjustable realsound ring tones
[Ue] rated operational voltage	18...24 V DC central power supply 12 V AC decentralized power feed 18...24 V DC decentralized power feed
Width	221 mm
Height	91 mm
Depth	24 mm
Net weight	0.263 kg

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...80 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	15.4 cm
Package 1 Length	24.3 cm
Package 1 Weight	578 g

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information