



### Main

Range	Exxact
Product or component type	Dimmer
Colour tint	White (RAL 9003)
Quantity per set	Set of 1

### Complementary

Device presentation	Complete product
Device mounting	Flush
Device application	Light control
Switch function	1-pole 2-way
Dimmer type	Transistor
Dimmer control	Rotary push type
Fixing mode	By screws
Rated current	10 A
[Ue] rated operational voltage	230 V
Network type	AC
Network frequency	50 Hz
Surface finish	Glossy
Load type	Incandescent lamp: 40...1000 W at 230 V AC Halogen lamp: 40...1000 W at 230 V AC Electronic transformer: 40...1000 W at 230 V AC
Protection type	Short-circuit protection Automatic overload protection
Connections - terminals	Screw terminals
Shape of screw head	Pozidriv No 1 and combi
Tightening torque	0.5 N.m
Clamping connection capacity	1 x 1.5...2 x 2.5 mm <sup>2</sup> for solid cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> for solid stranded cable(s)
Wire stripping length	6 mm
Material	ABS (acrylonitrile butadiene-styrene)
Height	71 mm
Width	71 mm
Embedding depth	29 mm
Product certifications	FIMKO[RETURN]CE[RETURN]NEMKO

### Environment

IP degree of protection	IP20 IP44 with additional sealing kit
IK degree of protection	IK02
Standards	EN 60669-2-1 EN 60669-1

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.400 cm
Package 1 Width	7.600 cm
Package 1 Length	7.800 cm
Package 1 Weight	82.000 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------