

Tehničke karakteristike proizvoda

Karakteristike

C1036M025

Zaštitna jedinica MicroLogic 6.2EM, ComPacT NSX100-250, 3P, elektronska osnovna i zemljospojna zaštita, motor, merenje energije, 25A



Osnovne informacije

Grupa proizvoda	ComPacT nove generacije
Grupa proizvoda	ComPacT NSX100...250 nova generacija
Tip proizvoda ili komponente	Zaštitna jedinica
Ime zaštitne jedinice	Micrologic 6.2 E-M
Tehnologija zaštitne jedinice	Elektronska
Kompatibilnost grupe proizvoda	ComPacT nova generacija NSX100 ComPacT nova generacija NSX160 ComPacT nova generacija NSX250
Primena uređaja	Motor
Broj polova	3P
Opis zaštićenih polova	3d
Funkcija zaštitne jedinice	LSIG
Tip zaštite	L : for zaštita od preopterećenja (dugotrajno) S : for kratkotrajna zaštita od kratkog spoja sa fiksnim kašnjenjem I : for trenutna zaštita od kratkog spoja G : for zaštita od zemljospoja
Trip unit rating	25 A pri 65 °C
[ue] nazivni napon	690 V AC 50/60 Hz
Tip mreže	AC
Mrežna frekvencija	50/60 Hz
Circuit breaker mounting mode	Fiksno

Dopunske informacije

Klasa motora	20 30 10 5
Dodatna motorna zaštita	Neuravnotežena struja Ukočeni rotor Podopterećenje Produženo vreme pokretanja
Long-time pick-up adjustment type Ir (thermal protection)	Podesivo 9 podešavanja
[Ir] long-time protection pick-up adjustment range	12...25 A
Long-time protection delay adjustment type tr	Podesivo

[tr] long-time protection delay adjustment range	120 Sekundi pri 1.5 x Ir 5 6,5 Sekundi pri 6 x Ir 5 5 Sekundi pri 7.2 x Ir 5 240 Sekundi pri 1.5 x Ir 10 13,5 Sekundi pri 6 x Ir 10 10 Sekundi pri 7.2 x Ir 10 480 Sekundi pri 1.5 x Ir 20 26 Sekundi pri 6 x Ir 20 20 Sekundi pri 7.2 x Ir 20 720 sekundi pri 1.5 x Ir 30
Termička memorija	20 minuta pre i nakon okidanja
Short-time protection pick-up adjustment type Isd	Podesivo, 9 podešavanja
[Isd] Short-time protection pick-up adjustment range	5...13 x Ir
Short-time protection delay adjustment type tsd	Fiksno
Instantaneous protection pick-up adjustment type li	Fiksno
[li] instantaneous protection pick-up adjustment range	425 A
Ground-fault protection pick-up adjustment type Ig	Podesivo
[Ig] ground-fault protection pick-up adjustment range	0.6...1 x In za In = 25 A Ig omogućavanje on/off
Ground-fault protection time delay adjustment type tg	Podesivo
[tg] ground-fault protection time delay adjustment range	0...0,4 sekundi
Diferencijalna zaštita	Bez
Zona selektivne blokade zsi	Sa
Lokalna signalizacija	Zauređaj spreman za rad: treperi LED (zelena) Zatemperatura iznad zadate tačke: LED 95 % lth (crvena)
Tip displeja	LCD displej
Tip merenja	Multimetar
Komunikacija podataka	Merenje električne energije Podešavanja zaštite i alarma Beleženje sa informacijom o vremenu podatka za istoriju uređaja i event tabelu Trenutne i angažovane vrednosti Indikatori vezani za održavanje Angažovane vrednosti struje i snage Kvalitet snage Maksimalno izmerene/minimalno izmerene veličine
Snimanje električnih podataka	Indikatori održavanja

Okruženje

Standardi	EN/IEC 60947-2
Klasa zaštite od električnog udara	Klasa II
Stepen zaprljanosti	3 u skladu sa IEC 60947-1
Ip stepen zaštite	IP40 u skladu sa IEC 60529
Temperatura okoline za rad uređaja	-25...70 °C
Temperatura okoline za skladištenje	-40...85 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9,8 cm
Package 1 Width	11,0 cm
Package 1 Length	15,0 cm
Package 1 Weight	540,0 g
Unit Type of Package 2	S03
Number of Units in Package 2	11
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	6,392 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
EU RoHS direktiva	У складу са изузецима
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka