

# TCSESM083F23F1

## ConneXium Extended Managed Switch - 8 ports for copper



### Main

Range of product	ConneXium
Product or component type	Ethernet TCP/IP managed switch
Concept	Transparent Ready
Communication port protocol	Ethernet TCP/IP SSH HTTP HTTPS SNMP RS232 LLDP Telnet SNTP MRP (Media Redundancy Protocol)
Port Ethernet	10/100BASE-TX - 8 port(s) copper cable
Maximum number of switches in cascade	Unlimited
Cybersecurity	Port hardening

### Complementary

Integrated connection type	Shielded RJ45 copper cable
Transmission support medium	Twisted shielded pairs cable CAT 5E for copper cable
Maximum cable distance between devices	100 m copper cable
Ethernet service	Configuration via web server VLAN Multicast filtering Data stream control IGMP Snooping SNMP-Traps and SYSLOG
Communication service	TFTP Quality of Service (QoS) Port monitoring Port mirroring Address conflict detection
Diagnostics run time	Signal contact Self test
Maximum number of switches in a ring	50
Redundancy	HiPER ring RSTP Redundant network coupling
[Us] rated supply voltage	24...48 V
Supply voltage limits	18...60 V DC SELV
Power consumption in W	10 W
Electrical connection	2 removable connectors 2 ways power supply
Mounting support	35 mm symmetrical DIN rail
Marking	CE UL RCM ATEX
Function available	Alarms (Traps) System information Report Trap log

Local signalling	1 dual colour LED (green/yellow) for P1 P2 power supplies 1 LED (red) for fault 1 dual colour LED (green/yellow) for ring manager 1 LED (red) for stand-by 1 LED (yellow) for signal contact 1 1 LED (yellow) for signal contact 2 1 LED per channel (green/yellow) for channel diagnostic Device status
Alarm output	2 voltfree contact 2 A
Alarm function	Power supply fault Data link status Temperature threshold External memory removed
Ethernet cabling system	TF switches
Width	120 mm
Height	137 mm
Depth	115 mm
Net weight	1 kg

## Environment

Ambient air temperature for operation	0...60 °C
Relative humidity	10...95 % non-condensing
IP degree of protection	IP30
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Standards	UL 508 EN/IEC 61131 IEC 61850-3 CSA C22.2 No 213 Class I Division 2 UL 1604 Class 1 Division 2
Product certifications	CE[RETURN]UL[RETURN]RCM[RETURN]ATEX[RETURN]LR[RETURN]GL[RETURN]BV

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.800 cm
Package 1 Width	22.500 cm
Package 1 Length	23.000 cm
Package 1 Weight	1.463 kg
Unit Type of Package 2	S04
Number of Units in Package 2	2
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	3.867 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions

