



Main

Range of product	Easy Modicon M200
Product or component type	Analogue input cartridge
Product compatibility	Easy Modicon M200
Analogue input number	2

Complementary

Analogue input type	Current 4...20 mA Current 0...20 mA Voltage 0...10 V
Analogue input resolution	12 bits
LSB value	2.44 mV 0...10 Vvoltage 4.88 µA 0...20 mAcurrent 3.91 µA 4...20 mAcurrent
Conversion time	20 ms
Sampling duration	10 ms
Absolute accuracy error	+/- 0.1 % of full scale at 25 °C +/- 1 % of full scale
Temperature drift	+/- 0.02 %FS/°C
Repeat accuracy	+/- 0.5 %FS
Non-linearity	+/- 0.01 %FS
Cross talk	<= 1 LSB
Type of cable	Twisted shielded pairs cable
Electrical connection	3 x 1.5 mm ² 2 screw terminal blocks with pitch 3.81 mm adjustment for inputs
Maximum cable distance between devices	Twisted shielded pairs cable: <30 m for input
Insulation	Non-insulated between analogue input and internal logic
Height	41 mm
Depth	15 mm
Width	35 mm
Net weight	0.012 kg
Permissible continuous overload	13 V, analogue input type: voltage 40 mA, analogue input type: current
Input impedance	<= 250 Ohm current >= 1 MOhm voltage

Environment

Immunity to microbreaks	10 ms
-------------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.589 cm
Package 1 Width	4.772 cm
Package 1 Length	7.056 cm
Package 1 Weight	30 g
Unit Type of Package 2	S02
Number of Units in Package 2	75
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.815 kg
Unit Type of Package 3	P12
Number of Units in Package 3	2400
Package 3 Height	100 cm
Package 3 Width	125 cm
Package 3 Length	55 cm
Package 3 Weight	85 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes