



## Main

|                               |                                               |
|-------------------------------|-----------------------------------------------|
| Range of product              | Telemecanique Limit switches XC Standard      |
| Series name                   | Standard format                               |
| Product or component type     | Limit switch                                  |
| Device short name             | XCKT                                          |
| Sensor design                 | Compact form A conforming to CENELEC EN 50047 |
| Body type                     | Fixed                                         |
| Head type                     | Rotary head                                   |
| Material                      | Plastic                                       |
| Body material                 | Plastic                                       |
| Head material                 | Zamak                                         |
| Fixing mode                   | By the body                                   |
| Movement of operating head    | Rotary                                        |
| Type of operator              | Spring return roller lever thermoplastic      |
| Type of approach              | Lateral approach, 2 directions                |
| Number of poles               | 2                                             |
| Contacts type and composition | 1 NC + 1 NO                                   |
| Contact operation             | Snap action                                   |

## Complementary

|                                        |                                                                                                                                                                                                                                                                                                                                                                        |
|----------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Tracks                                 | 24/40 mm                                                                                                                                                                                                                                                                                                                                                               |
| Switch actuation                       | By 30° cam                                                                                                                                                                                                                                                                                                                                                             |
| Electrical connection                  | Screw-clamp terminals, clamping capacity: 1 x 0.34...2 x 1.5 mm <sup>2</sup>                                                                                                                                                                                                                                                                                           |
| Cable entry                            | 2 entries tapped for M16 x 1.5 cable gland, cable outer diameter: 4...8 mm                                                                                                                                                                                                                                                                                             |
| Contacts insulation form               | Zb                                                                                                                                                                                                                                                                                                                                                                     |
| Positive opening                       | With                                                                                                                                                                                                                                                                                                                                                                   |
| Positive opening minimum torque        | 0.25 N.m                                                                                                                                                                                                                                                                                                                                                               |
| Minimum torque for tripping            | 0.1 N.m                                                                                                                                                                                                                                                                                                                                                                |
| Maximum actuation speed                | 1.5 m/s                                                                                                                                                                                                                                                                                                                                                                |
| Repeat accuracy                        | 0.1 mm on the tripping points with 1 million operating cycles                                                                                                                                                                                                                                                                                                          |
| Contact code designation               | A300, AC-15 (Ue = 240 V), Ie = 3 A, Ithe = 10 A conforming to IEC 60947-5-1 appendix A<br>Q300, DC-13 (Ue = 250 V), Ie = 0.27 A conforming to IEC 60947-5-1 appendix A                                                                                                                                                                                                 |
| [Ui] rated insulation voltage          | 300 V conforming to UL 508<br>500 V (pollution degree 3) conforming to IEC 60947-1<br>300 V conforming to CSA C22.2 No 14                                                                                                                                                                                                                                              |
| Maximum resistance across terminals    | 25 MOhm conforming to IEC 60255-7 category 3                                                                                                                                                                                                                                                                                                                           |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to IEC 60664<br>6 kV conforming to IEC 60947-1                                                                                                                                                                                                                                                                                                         |
| Short-circuit protection               | 10 A cartridge fuse, type gG                                                                                                                                                                                                                                                                                                                                           |
| Electrical durability                  | 5000000 Cycles, DC-13, 120 V, 4 W, operating rate <60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C<br>5000000 Cycles, DC-13, 24 V, 10 W, operating rate <60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C<br>5000000 cycles, DC-13, 48 V, 7 W, operating rate <60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C |
| Mechanical durability                  | 10000000 cycles                                                                                                                                                                                                                                                                                                                                                        |

|                               |                        |
|-------------------------------|------------------------|
| Width                         | 58 mm                  |
| Height                        | 51 mm                  |
| Depth                         | 30 mm                  |
| Net weight                    | 0.145 kg               |
| Terminals description ISO n°1 | (21-22)NC<br>(13-14)NO |

## Environment

|                                       |                                                                        |
|---------------------------------------|------------------------------------------------------------------------|
| Shock resistance                      | 50 gn for 11 ms conforming to IEC 60068-2-27                           |
| Vibration resistance                  | 25 gn (f= 10...500 Hz) conforming to IEC 60068-2-6                     |
| IP degree of protection               | IP66 conforming to IEC 60529<br>IP67 conforming to IEC 60529           |
| IK degree of protection               | IK04 conforming to IEC 62262                                           |
| Electrical shock protection class     | Class II conforming to IEC 61140<br>Class II conforming to NF C 20-030 |
| Ambient air temperature for operation | -25...70 °C                                                            |
| Ambient air temperature for storage   | -40...70 °C                                                            |
| Protective treatment                  | TC                                                                     |
| Product certifications                | UL[RETURN]CSA[RETURN]CCC                                               |
| Standards                             | UL 508<br>IEC 60204-1<br>CSA C22.2 No 14<br>IEC 60947-5-1              |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 5.800 cm  |
| Package 1 Width              | 6.800 cm  |
| Package 1 Length             | 12.000 cm |
| Package 1 Weight             | 148.000 g |
| Unit Type of Package 2       | S02       |
| Number of Units in Package 2 | 24        |
| Package 2 Height             | 15.000 cm |
| Package 2 Width              | 30.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 4.083 kg  |

## Offer Sustainability


|                            |                                                                                                                       |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                 |
| REACH Regulation           |  <a href="#">REACH Declaration</a> |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)                                                            |
| Mercury free               | Yes                                                                                                                   |
| RoHS exemption information |  <a href="#">Yes</a>               |

## Contractual warranty


|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Dimensions

mm  
in.



mm  
in.



- (1) Tapped entry for M16 x 1.5
- (2) 4 elongated holes Ø 4.3 x 6.3 mm on 22/42mm ctrs, 4 holes Ø 4.3 on 20/40 mm ctrs.
- (3) 2 x Ø 3 holes for support studs, depth 4 mm.

## Mounting with Cable Entry

### Position of Cable Gland



- (1) Recommended
- (2) To be avoided


## Mounting with Rotary Heads and Levers

### Type of Cam



- (1) Recommended
- (2) To be avoided

## Setting-up with Head ZCE01 and ZCE09



- (1) Tightening torque (Min : 1) (Max : 1.5)
- (2) Tightening torque (Min : 0.8) (Max : 1.2)

---

## Wiring Diagram


---

2-pole NC + NO Snap Action




## Characteristics of Actuation

### Switch Actuation by 30° Cam



## Functionnal Diagram



- (P) Positive opening point  
 (1) NC contact with positive opening operation  
 (2) Closed  
 (3) Open  
 (4) Tripping  
 (5) Resetting