

Product data sheet

Characteristics

DE1DS1A13

Empty enclosures for standard starters, TeSys LE, with 1 pushbutton and 1 knob, for LE1D09 and LE1D12



Main

Range of product	TeSys
Range	TeSys
Device short name	DE1D
Product or component type	Enclosure
Material	Polycarbonate
Device composition	Contactors ordered separately Thermal overload relay ordered separately
Product compatibility	LE1D12 LE1D09
Control type	Push-button reset blue R Selector switch 2 positions start/stop O-I

Complementary

Cable entry number	2 ISO20 top 2 ISO20 bottom 2 Pg 13 bottom 2 Pg 16 bottom
Height	166 mm
Width	88 mm
Depth	165 mm
Net weight	0.3 kg




Environment

IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment
Product certifications	UKCA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.0 cm
Package 1 Width	15.5 cm
Package 1 Length	20.5 cm
Package 1 Weight	551.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information