

Product data sheet

Characteristics

DE1KS217A06A29

TeSys LG - enclosure for DOL starter - with 2 pushbuttons - padlocking



Main

Range of product	TeSys
Range	TeSys
Device short name	DE1K
Product or component type	Enclosure
Device application	Motor
Material	Polycarbonate
Device composition	Contacteur ordered separately Circuit-breaker ordered separately Padlocking device
Product compatibility	LG7
Control type	Push-button start white I Push-button stop black O

Complementary

Device mounting	Surface
Cable entry number	4 2 Pg 13 + 2 Pg 16 top 4 2 Pg 13 + 2 Pg 16 bottom
Height	165 mm
Width	175 mm
Depth	142 mm
Net weight	0.5 kg




Environment



IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Environmental characteristic	Standard environment
Product certifications	UKCA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25.0 cm
Package 1 Width	25.0 cm
Package 1 Length	25.1 cm
Package 1 Weight	1.08 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Contractual warranty	
Warranty	18 months