



### Main

Range of product	Harmony 9001SK
Product or component type	Illuminated push-button
Device short name	9001SK
Type of operator	Spring return
Operator profile	Clear mushroom Ø 35 mm, unmarked
Operator additional information	Screw-on plastic mushroom
Light block supply	Via integral transformer 120 V AC/DC

### Complementary

Bezel material	Plastic
Mounting diameter	30 mm
Light source	incandescent
Bulb base	BA 9s
[Us] rated supply voltage	120 V AC
Contacts type and composition	1 C/O
Connections - terminals	Screw clamp terminals 1 x 0.22...2 x 1.5 mm <sup>2</sup> conforming to EN/IEC 60947-1
Tightening torque	0.8 N.m conforming to EN/IEC 60947-1
Shape of screw head	Cross slotted
Mechanical durability	5000000 cycles
Operating position	Any position
[Ui] rated insulation voltage	250 V (pollution degree 3) conforming to EN/IEC 60947-1
[Uimp] rated impulse withstand voltage	2.5 kV conforming to EN/IEC 60947-1
Contacts material	Silver alloy contacts
Contact operation	Standard
Positive opening	Without
Short-circuit protection	10 A cartridge fuse conforming to EN/IEC 60947-5-1
[Ith] conventional free air thermal current	10 A
[Icm] rated short-circuit making capacity	0.1 KA at 240 V DC-13, 7200 VA 15 KA at 480 V AC-15, 7200 VA 30 KA at 240 V AC-15, 7200 VA 60 KA at 120 V AC-15, 7200 VA 0.27 KA at 250 V DC-13 0.55 KA at 125 V DC-13 0.1 KA at 600 V DC-13
Rated breaking capacity	1.2 KA at 600 V AC-15, 720 VA 1.5 KA at 480 V AC-15, 720 VA 3 KA at 240 V AC-15, 720 VA 6 KA at 120 V AC-15, 720 VA 0.27 KA at 250 V DC-13 0.55 KA at 125 V DC-13 0.1 KA at 600 V DC-13
Net weight	0.181 kg
Device presentation	Complete product

## Environment

Standards	UL 508 EN/IEC 60947-5-1 EN/IEC 60947-5-4 CSA C22.2 No 14 EN/IEC 60947-1 JIS C 4520 JIS C 852
Product certifications	NEMA[RETURN]UL 508
Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Vibration resistance	7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn conforming to IEC 60068-2-27
Electrical shock protection class	Class II conforming to IEC 61140
IP degree of protection	IP66 conforming to IEC 60529
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X