

GVAD1001

Add-on contact block, TeSys Deca Frame
2/3, 1NO(fault)+1NC, side, for GV2/GV3(except GV3ME)



Main

Range	TeSys TeSys Deca
Device short name	GVAD
Product or component type	Auxiliary contact block
Product compatibility	GV2P GV2LE GV3L GV2ME GV2RT GV3P GV2L
Mounting location	Left side
Auxiliary contacts operation	Fault signal 1 NO
Pole contact composition	1 NO + 1 NC

Complementary

[Ui] rated insulation voltage	690 V conforming to IEC 60947-1 300 V conforming to UL 508 300 V conforming to CSA C22.2 No 14
[Ue] rated operational voltage	48...690 V AC 24...240 V DC
[Ith] conventional free air thermal current	6 A 2.5 A for fault signalling
Mechanical durability	100000 cycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Protection type	GB2CB... circuit breaker GG fuse 10 A
Rated operational power in VA	300 VA at 48 V AC-15 - electrical durability: 100000 cycles 414 VA at 690 V AC-15 - electrical durability: 100000 cycles 500 VA at 110...127 V AC-15 - electrical durability: 100000 cycles 500 VA at 500 V AC-15 - electrical durability: 100000 cycles 650 VA at 440 V AC-15 - electrical durability: 100000 cycles 720 VA at 230...240 V AC-15 - electrical durability: 100000 cycles 850 VA at 380...415 V AC-15 - electrical durability: 100000 cycles 36 VA at 24 V AC-14 - electrical durability: 1000 cycles 48 VA at 48 V AC-14 - electrical durability: 1000 cycles 72 VA at 110...127 V AC-14 - electrical durability: 1000 cycles
Rated operational power in W	120 W at 240 V DC-13 - electrical durability: 100000 cycles 140 W at 110 V DC-13 - electrical durability: 100000 cycles 140 W at 24 V DC-13 - electrical durability: 100000 cycles 180 W at 60 V DC-13 - electrical durability: 100000 cycles 240 W at 48 V DC-13 - electrical durability: 100000 cycles 15 W at 48 V DC-13 - electrical durability: 1000 cycles 24 W at 24 V DC-13 - electrical durability: 1000 cycles 9 W at 60 V DC-13 - electrical durability: 1000 cycles
Tightening torque	1.4 N.m - on screw clamp terminals
Height	89 mm
Width	9.3 mm
Depth	66 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Net weight	0.055 kg
Colour	Dark grey







Environment

Environmental characteristic	Normal environment
Product certifications	UKCA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	6.500 cm
Package 1 Length	9.000 cm
Package 1 Weight	46.500 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.500 cm
Package 2 Width	9.500 cm
Package 2 Length	15.000 cm
Package 2 Weight	516.000 g
Unit Type of Package 3	S02
Number of Units in Package 3	60
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	3.347 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

GVAD1001

