

Product data sheet

Characteristics

DE1DS2A13

TeSys LE - enclosure for DOL starter - with selector switch and pushbutton



Main

| | |
|---------------------------|--|
| Range of product | TeSys |
| Range | TeSys |
| Device short name | DE1D |
| Product or component type | Enclosure |
| Material | Polycarbonate |
| Device composition | Contacteur ordered separately Thermal overload relay ordered separately |
| Product compatibility | LE1D18...35 |
| Control type | Push-button reset blue R Selector switch 2 positions start/stop O-I |

Complementary

| | |
|--------------------|--|
| Cable entry number | 2 ISO20 top 2 ISO20 bottom 2 Pg 16 bottom 2 ISO25 top 2 Pg 21 bottom 2 ISO25 bottom |
| Height | 201 mm |
| Width | 103 mm |
| Depth | 170 mm |
| Net weight | 0.5 kg |

Environment

| | |
|---------------------------------------|------------------------------|
| IP degree of protection | IP65 conforming to IEC 60529 |
| IK degree of protection | IK07 conforming to IEC 60529 |
| Ambient air temperature for operation | -5...40 °C |
| Environmental characteristic | Standard environment |
| Product certifications | UKCA |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 14.5 cm |
| Package 1 Width | 16.0 cm |
| Package 1 Length | 21.0 cm |
| Package 1 Weight | 660.0 g |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|