

Product data sheet

Characteristics

LE3K095P7

TeSys LE - enclosed star-delta starter - 9 A -
230 V AC coil



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE3K
Product or component type	Enclosed star-delta starter
Device application	Standard
Material	Polycarbonate
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Star-delta contactors Mechanical interlock
Motor power kW	4 kW at 220 V AC 50/60 Hz 7.5 kW at 380/400 V AC 50/60 Hz 7.5 kW at 415 V AC 50/60 Hz 7.5 kW at 440 V AC 50/60 Hz
[Uc] control circuit voltage	230 V AC 50/60 Hz
Control type	Push-button start green I Push-button stop/reset red O

Complementary

Cable entry number	4 2 Pg 13 + 2 Pg 16 top 4 ISO20 top 4 2 Pg 13 + 2 Pg 16 bottom 4 ISO20 bottom
Width	175 mm
Height	165 mm
Depth	146 mm
Net weight	1.46 kg

Environment

IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

Warranty	18 months
----------	-----------