



Main

Range of product	INS320...630
Range	TransferPacT ComPact
Device short name	INS320
Product or component type	Manual transfer switch
Device application	Change source of supply
Range compatibility	ComPact ComPacT INS INS320 switch disconnecter
Poles description	3P
Network type	AC DC
Network frequency	50/60 Hz
Mounting mode	Fixed
Upside connection	Front
Downside connection	Front
Suitability for isolation	Yes
Contact position indicator	Yes
[Icm] rated short-circuit making capacity	330 kA with upstream protection circuit breaker 690 V AC at 50/60 Hz 50 kA switch-disconnector alone 690 V AC at 50/60 Hz

Complementary

Transfer switch class	PC
Number of contact position	3
Control type	Direct front rotary handle
Operating mode	Manual
Mounting support	Plate Rail
Locking options description	Padlocking in OFF position
[Ie] rated operational current	AC-22A: 320 A AC 50/60 Hz 220/240 V AC-22A: 320 A AC 50/60 Hz 380/415 V AC-22A: 320 A AC 50/60 Hz 440/480 V AC-22A: 320 A AC 50/60 Hz 500/525 V AC-22A: 320 A AC 50/60 Hz 660/690 V AC-23A: 320 A AC 50/60 Hz 220/240 V AC-23A: 320 A AC 50/60 Hz 380/415 V AC-23A: 320 A AC 50/60 Hz 440/480 V AC-23A: 320 A AC 50/60 Hz 500/525 V AC-23A: 320 A AC 50/60 Hz 660/690 V DC-22A: 320 A DC 125 V 2 poles in series DC-23A: 320 A DC 125 V 2 poles in series
[Ith] conventional free air thermal current	320 A at 60 °C
Rated duty	Uninterrupted
Intermittent duty class	Class 120 - 60 %
[Ui] rated insulation voltage	750 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-3 125 V DC conforming to IEC 60947-3
Mechanical interlocking	With mechanical interlocking
Mechanical durability	10000 cycles

Electrical durability	AC-22A: 1500 cycles 440 V AC 50/60 Hz AC-22A: 1500 cycles 500 V AC 50/60 Hz AC-22A: 1500 cycles 690 V AC 50/60 Hz AC-23A: 1500 cycles 440 V AC 50/60 Hz AC-23A: 1500 cycles 500 V AC 50/60 Hz AC-23A: 1500 cycles 690 V AC 50/60 Hz DC-23A: 1000 cycles 125 V DC 2 poles in series
Connection pitch	45 mm
[Icw] rated short-time withstand current	11.5 kA during 3 s conforming to IEC 60947-3 20 kA during 1 s conforming to IEC 60947-3 4 kA during 30 s conforming to IEC 60947-3 4.9 kA during 20 s conforming to IEC 60947-3
Height	205 mm
Width	395 mm
Depth	155 mm
Net weight	13.5 kg

Environment

Standards	IEC 60947-3 IEC 60947-1
Product certifications	CB
Electrical shock protection class	Class II
IP degree of protection	IP40 conforming to IEC 60947-3
Pollution degree	3
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	23.000 cm
Package 1 Width	50.000 cm
Package 1 Length	23.000 cm
Package 1 Weight	13.815 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------