

Osnovno

Ponuda	Fupact
Naziv proizvoda	Fupact ISFT
Skraćeno ime uređaja	ISFT400
Vrsta proizvoda ili dijela	Prekidač sa osiguračima
Namjena uređaja	Distribucija Zaštita, nadzor i upravljanje
Opis polova	3P
Number of fuse carriers	3
Tip rastalnog osigurača	DIN
Veličina rastalnog osigurača	NH2
Prikladnost za izolaciju	Da
Providni prekidač	Da
[Ithe] propisana termalna struja pri okolnoj temperaturi zraka	280 A 70 °C) vodoravno 280 A 70 °C) vertikalno 300 A 65 °C) vodoravno 300 A 65 °C) vertikalno 320 A 60 °C) vodoravno 320 A 60 °C) vertikalno 340 A 55 °C) vodoravno 340 A 55 °C) vertikalno 360 A 50 °C) vodoravno 360 A 50 °C) vertikalno 380 A 45 °C) vodoravno 380 A 45 °C) vertikalno 400 A 40 °C) 34 W 400 A 40 °C) vodoravno 400 A 40 °C) vertikalno
[Ithe] propisana termalna struja specifičnih kućišta	400 A 40 °C 34 W
[Ue] radni nazivni napon	440 V DC 690 V AC 50/60 Hz 800 V AC 50/60 Hz AC-20 800 V DC DC-20
[Ui] nazivni napon izolacije	800 V AC 50/60 Hz 800 V DC
[Uimp] nazivni impulsni podnosivi napon	8 kV
[Ie] nazivna pogonska struja	AC-21B: 400 A at 220/240 V AC 50/60 Hz AC-21B: 400 A at 380/415 V AC 50/60 Hz AC-21B: 400 A at 440/480 V AC 50/60 Hz AC-21B: 400 A at 500 V AC 50/60 Hz AC-21B: 400 A at 660/690 V AC 50/60 Hz AC-22B: 400 A at 220/240 V AC 50/60 Hz AC-22B: 400 A at 380/415 V AC 50/60 Hz DC-21B: 400 A at 125 V DC (1 pol) DC-21B: 400 A at 220 V DC (1 pol) DC-21B: 400 A at 440 V DC (2 pola u seriji)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Dodatno

[Icm] Rated short-circuit making capacity	Icm 105 kA 500 V Icm 105 kA 690 V Icn 50 kA 500 V Icn 50 kA 690 V Icm 105 kA 415 V Icn 50 kA 415 V
Nazivni rad	Neprekidni
Tip upravljanja	Ručka nosača osigurača
Dodatak za zaključavanje	3 lokota
Monterški držač	Sabirnice
Mjesto za montažu	Usporedno
Operacija kontakta	Jednstruko prekidanje
Mehanička izdržljivost	1000 ciklus/a
Električna izdržljivost	AC-21B 200 ciklus/a 690 V AC 50/60 Hz AC-22B 200 ciklus/a 415 V AC 50/60 Hz
Priključci - stezaljke	Ovješanjem 400 A 60 mm
Širina	210 mm
Visina	271 mm
Dubina	127 mm
Standardi	EN/IEC 60947-1 EN/IEC 60947-3 IEC 60269-2-1
Certifikati proizvoda	KEMA-KEUR

Okolina

IP stupanj zaštite	IP20 conforming to IEC 60529
IK stupanj zaštite	IK07u skladu s EN 50102
Stupanj onečišćenja	3 u skladnosti sa IEC 60947
Okolišna temperatura zraka pri radu	-25...70 °C
Okolišna temperatura zraka pri skladištenju	-50...85 °C

Broj pakirnih jedinica

Mjerna jedinica Paketa 1	PCE
Broj Jedinica u Paketu 1	1

Održivost ponude

Direktiva EU RoHS	Sukladno  Izjava EU RoHS
Bez otrovnih teških metala	Da
Bez žive	Da
Propis RoHS za Kinu	 Izjava RoHS Za Kinu
Informacije o RoHS izuzeću	 Da
Izjava o očuvanju okoliša	 Ekološki Profil Proizvoda

Ugovorno jamstvo

Jamstvo	18 months
---------	-----------