

# ATV11HU18M2A

variable speed drive ATV11 - 0.75kW - 230V 1-phase supply - IP20



## Main

|                                    |                                                                                                                                                                                                                                                              |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range of product                   | Altivar                                                                                                                                                                                                                                                      |
| Product or component type          | Variable speed drive                                                                                                                                                                                                                                         |
| Product specific application       | Simple machine                                                                                                                                                                                                                                               |
| Component name                     | ATV11                                                                                                                                                                                                                                                        |
| Application market                 | Asia                                                                                                                                                                                                                                                         |
| Assembly style                     | With heat sink                                                                                                                                                                                                                                               |
| EMC filter                         | Without EMC filter                                                                                                                                                                                                                                           |
| Built-in fan                       | Without                                                                                                                                                                                                                                                      |
| Network number of phases           | Single phase                                                                                                                                                                                                                                                 |
| [Us] rated supply voltage          | 200...240 V - 15...10 %                                                                                                                                                                                                                                      |
| Supply frequency                   | 50...60 Hz - 5...5 %                                                                                                                                                                                                                                         |
| Motor power kW                     | 0.75 kW                                                                                                                                                                                                                                                      |
| Line current                       | 9.9 A at 200 V, I <sub>sc</sub> = 1 kA                                                                                                                                                                                                                       |
| Nominal output current             | 1.4 A 230 V motor 4 kHz                                                                                                                                                                                                                                      |
| Maximum transient current          | 6 A for 60 s                                                                                                                                                                                                                                                 |
| Power dissipation in W             | 40 W at nominal load                                                                                                                                                                                                                                         |
| Switching frequency                | 2...16 kHz adjustable<br>4...16 kHz with derating factor                                                                                                                                                                                                     |
| Braking torque                     | 150 % of nominal motor torque with braking resistor at high inertia<br>20 % of nominal motor torque without braking resistor at no load<br>80 % of nominal motor torque with braking resistor at no load                                                     |
| Asynchronous motor control profile | Sensorless flux vector control with PWM type motor control signal                                                                                                                                                                                            |
| Electrical connection              | Terminal, clamping capacity: 1.5 mm <sup>2</sup> , AWG 14 (AI1, RA-RC, LI1...LI4, DO)<br>Terminal, clamping capacity: 1.5 mm <sup>2</sup> , AWG 14 (L1, L2, L3, U, V, W, PA, PC)                                                                             |
| Supply                             | Internal supply for logic inputs: 15 V (+/- 15 %) 100 mA, protection type: overload and short-circuit protection<br>Internal supply for reference potentiometer (2.2 to 10 kOhm): 5...5.25 VDC 10 mA, protection type: overload and short-circuit protection |
| Analogue input type                | Configurable current AI1 4...20 mA 250 Ohm without adding resistor<br>Configurable voltage AI1 0...5 V 40000 Ohm only with internal supply<br>Configurable current AI1 0...20 mA 250 Ohm<br>Configurable voltage AI1 0...10 V 40000 Ohm                      |
| Sampling duration                  | AI1: 20 ms analog<br>LI1...LI4: 20 ms discrete                                                                                                                                                                                                               |
| Response time                      | 20 ms DO                                                                                                                                                                                                                                                     |
| Linearity error                    | DO: +/- 1 % for output<br>AI: +/- 5 % for input                                                                                                                                                                                                              |
| Discrete input type                | Assignable LI1 forward 5000 Ohm 15 V 24 V<br>Assignable LI2 reverse 5000 Ohm 15 V 24 V<br>Assignable LI3/LI4 4 preset speeds 5000 Ohm 15 V 24 V                                                                                                              |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

|                                       |                                                                                                                                                                                                                                                                                                                                                                         |
|---------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Discrete input logic                  | Positive logic (source) (LI1...LI4), < 5 V (state 0), > 11 V (state 1)<br>Logic input not wired (LI1...LI4), < 5 V (state 1)<br>Negative logic (source) (LI1...LI4), > 11 V (state 0)                                                                                                                                                                                   |
| Discrete output type                  | Assignable as external voltage DO 30 V max, 30 mA<br>Assignable as open collector logic output DO 100 Ohm, 50 mA max<br>Factory set as PWM open collector output DO at 2 kHz 10 mA max<br>Protected relay logic RA-RC 1 NO<br>Assignable as internal voltage DO                                                                                                         |
| Minimum switching current             | RA-RC 10 mA at 24 V DC                                                                                                                                                                                                                                                                                                                                                  |
| Maximum switching current             | 2 A 250 V AC inductive $\cos \phi = 0.4$ 7 ms RA-RC<br>2 A 30 V DC inductive $\cos \phi = 0.4$ 7 ms RA-RC<br>5 A 250 V AC resistive $\cos \phi = 1$ RA-RC<br>5 A 30 V DC resistive $\cos \phi = 1$ RA-RC                                                                                                                                                                |
| Protection type                       | Line supply overvoltage: drive<br>Line supply undervoltage: drive<br>Overcurrent between output phases and earth: drive<br>Overheating protection: drive<br>Short-circuit between motor phases: drive<br>Thermal protection: motor                                                                                                                                      |
| Frequency resolution                  | Display unit: 0.1 Hz<br>Analog input: converter A/D, 10 bits                                                                                                                                                                                                                                                                                                            |
| Electromagnetic compatibility         | 1.2/50 $\mu$ s - 8/20 $\mu$ s surge immunity test level 3 conforming to EN/IEC 61000-4-5<br>Electrical fast transient/burst immunity test level 4 conforming to EN/IEC 61000-4-4<br>Electrostatic discharge immunity test level 3 conforming to EN/IEC 61000-4-2<br>Radiated radio-frequency electromagnetic field immunity test level 3 conforming to EN/IEC 61000-4-3 |
| Maximum motor cable length            | 20 M with additional EMC filter from 2 to 16 kHz conforming to EN 55011 class A group 1<br>5 m with additional EMC filter from 2 to 16 kHz conforming to EN 55011 class B                                                                                                                                                                                               |
| Vibration resistance                  | 1 gn ( $f = 13 \dots 200$ Hz) conforming to EN/IEC 60068-2-6<br>1.5 mm peak to peak ( $f = 3 \dots 13$ Hz) conforming to EN/IEC 60068-2-6                                                                                                                                                                                                                               |
| Shock resistance                      | 15 gn for 11 ms conforming to EN/IEC 60068-2-27                                                                                                                                                                                                                                                                                                                         |
| Relative humidity                     | 5...93 % without condensation conforming to IEC 60068-2-3<br>5...93 % without dripping water conforming to IEC 60068-2-3                                                                                                                                                                                                                                                |
| Ambient air temperature for operation | -10...40 °C without derating<br>40...50 °C by removing the protective cover from the top of the drive<br>50...60 °C by removing the protective cover from the top of the drive with current derating of 2.2 % per °C                                                                                                                                                    |
| Operating altitude                    | $\leq 1000$ m without derating<br>> 1000 m with current derating 1 % per 100 m                                                                                                                                                                                                                                                                                          |

## Complementary

|                              |                                                                                                                                                               |
|------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product destination          | Asynchronous motors                                                                                                                                           |
| Supply voltage limits        | 170...264 V                                                                                                                                                   |
| Network frequency limits     | 47.5...63 Hz                                                                                                                                                  |
| Speed drive output frequency | 0...200 Hz                                                                                                                                                    |
| Nominal switching frequency  | 4 kHz                                                                                                                                                         |
| Speed range                  | 1...20                                                                                                                                                        |
| Transient overtorque         | 150...170 % of nominal motor torque                                                                                                                           |
| Regulation loop              | Factory-set with the speed loop stability and gain<br>Adjustable frequency<br>Possible correction for machines with high resistive torque/inertia/fast cycles |
| Motor slip compensation      | Preset in factory<br>Adjustable                                                                                                                               |
| Prospective line $I_{sc}$    | 1 kA                                                                                                                                                          |

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| Output voltage                      | <= 2 x power supply voltage          |
| Insulation                          | Electrical between power and control |
| Analogue input number               | 1                                    |
| Discrete input number               | 4                                    |
| Discrete output number              | 2                                    |
| Acceleration and deceleration ramps | Linear from 0 to 99.9 s              |
| Braking to standstill               | By DC injection                      |
| Insulation resistance               | > 500 MOhm                           |
| Marking                             | CE                                   |
| Operating position                  | Vertical +/- 10 degree               |
| CAD overall width                   | 72 mm                                |
| CAD overall height                  | 142 mm                               |
| CAD overall depth                   | 145 mm                               |
| Net weight                          | 1.1 kg                               |

## Environment

|                                     |                                         |
|-------------------------------------|-----------------------------------------|
| Standards                           | EN 50178                                |
| Product certifications              | C-Tick[RETURN]UL[RETURN]CSA[RETURN]N998 |
| IP degree of protection             | IP20                                    |
| Ambient air temperature for storage | -25...65 °C                             |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|