



Main

Range	ComPact
Product name	ComPact NSX
Range of product	ComPact NSX100...250
Device short name	NSX250N
Product or component type	Circuit breaker
Device application	Distribution
Number of poles	1P
Protected poles description	1t
[In] rated current	200 A at 40 °C
[Ue] rated operational voltage	277 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Utilisation category	Category A
[Icu] rated ultimate short-circuit breaking capacity	25 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Performance level	N 25 kA 240 V AC
Trip unit name	TM-D
Trip unit technology	Thermal-magnetic
Control type	Toggle
Circuit breaker mounting mode	Fixed

Complementary

[Ui] rated insulation voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ics] rated service short-circuit breaking capacity	25 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical durability	10000 cycles
Electrical durability	5000 Cycles at 440 V In 10000 cycles at 440 V In/2
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Connection pitch	35 mm
Protection type	For overload protection (thermal) For short-circuit protection (magnetic)
Trip unit rating	200 A at 40 °C
Long-time pick-up adjustment type Ir (thermal protection)	Fixed
[Ir] long-time protection pick-up adjustment range	1 In
[Im] magnetic protection pick-up range	850 A
Earth-leakage protection	Without
Width (W)	35 mm
Height (H)	161 mm
Depth (D)	86 mm






Environment

Standards	EN/IEC 60947
Product certifications	CCC[RETURN]EAC[RETURN]Marine
Overvoltage category	Class II
Electrical shock protection class	Class II
Pollution degree	3 conforming to IEC 60664-1
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C
Relative humidity	0...95 %
Operating altitude	0...2000 m without derating 2000 m...5000 m with derating

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.3 cm
Package 1 Width	13.0 cm
Package 1 Length	17.5 cm
Package 1 Weight	766.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	24
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	18.849 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------