



### Main

Range of product	EasyPact
Range	EasyPact
Device short name	busbar
Product or component type	Busbar
Device application	Connection
Range compatibility	EasyPact EasyPact EZB circuit breaker
[In] rated current	400 A
Number of ways	10 ways

### Complementary

[Ui] rated insulation voltage	690 V AC 50/60 Hz
[Ue] rated operational voltage	550 V AC 50/60 Hz
Number of devices	10 (3P) 14 (2P) 30 (1P)
Busbar extension	2 or 4 ways
[Icw] rated short-time withstand current	40 kA for 1 s
Height	515 mm
Width	416 mm
Depth	107 mm

### Environment

Standards	IEC 60439
-----------	-----------

### Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------