



Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Switch
Device presentation	Mechanism
Technology type	Electromechanical
Switch function	1-pole 1-way
Number of rocker	1
Device application	Light control
Provided equipment	Internal power connection
Colour tint	White

Complementary

Rated current	10 AX
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Electrical durability	10000 cycles
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	2 modules
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 Mm² rigid cable 0...2.5 mm² flexible cable
Material	ASA + PC: mechanism cover
Fixing mode	Clip-in
Width	45 mm
Height	45 mm
Depth	34 mm
Embedding depth	22 mm
Net weight	0.0204 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	EMC directive EN 60669-1 LV directive
Product certifications	14.10.01/5433






Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Window-cleaning fluid UV resistant Oil Petrol Bleach Alcohol Acetone Liquid soap

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	6.500 cm
Package 1 Length	6.500 cm
Package 1 Weight	24.300 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.500 cm
Package 2 Width	13.500 cm
Package 2 Length	33.500 cm
Package 2 Weight	306.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	4.220 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------