



Main

Range	Thalassa
Product name	Thalassa PLA
Enclosure type	Multi-purpose
Product or component type	Suitable enclosure
Version	PLAT
Nominal height	1250 mm
Nominal width	750 mm
Nominal depth	420 mm
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 2 side part 1 rear panel 1 door 1 canopy

Complementary

Body type	Open top and sealed bottom part assembled with side parts
Door type	Plain front
Number of doors	1 door(s)
Door opening side	Reversible (120 °)
Lock type	4 points lock, handle with 5 mm double bar insert
Accessibility for operation	Front Top Rear
Removable parts	Door by hinges Rear panel by fixing element Canopy by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	Veritas
Electrical insulation class	Class II

Environment

IP degree of protection	IP44 conforming to IEC 60529 (with ventilated canopy)
IK degree of protection	IK10 conforming to IEC 62262 (plain door)
Fire resistance	960 °C conforming to IEC 62208
Ambient air temperature for storage	-35...90 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	126.0 cm
Package 1 Width	78.0 cm
Package 1 Length	48.0 cm

Package 1 Weight	45.188 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	2
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	140 cm
Package 2 Weight	89 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations