

# LAD9R1V

Kit for assembling 3P reversing  
contactors, LC1D09-D38 with screw clamp  
terminals, with electrical interlock



## Main

|                           |  |
|---------------------------|--|
| Range of product          | TeSys Deca   |
| Range                     | TeSys<br>Linergy   |
| Device short name         | LAD9   |
| Product or component type | Kits for reversing contactor                             |
| Poles description         | 3P   |
| Range compatibility       | TeSys TeSys D contactor<br>TeSys TeSys Deca              |
| Product compatibility     | LC1D09<br>LC1D12<br>LC1D18<br>LC1D25<br>LC1D32<br>LC1D38 |

## Complementary

|                 |  |
|-----------------|--|
| Kit composition | Electrical and mechanical interlock<br>Set of power connection |
| Net weight      | 0.045 kg   |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 8 cm      |
| Package 1 Width              | 2.5 cm    |
| Package 1 Length             | 9.3 cm    |
| Package 1 Weight             | 70 g      |
| Unit Type of Package 2       | BB1       |
| Number of Units in Package 2 | 10        |
| Package 2 Height             | 9.6 cm    |
| Package 2 Width              | 9.8 cm    |
| Package 2 Length             | 15 cm     |
| Package 2 Weight             | 726 g     |
| Unit Type of Package 3       | S03       |
| Number of Units in Package 3 | 140       |
| Package 3 Height             | 30 cm     |
| Package 3 Width              | 30 cm     |
| Package 3 Length             | 40 cm     |
| Package 3 Weight             | 10.664 kg |

## Offer Sustainability

|                        |                                |
|------------------------|--------------------------------|
| REACH Regulation       | REACH Declaration              |
| REACH free of SVHC     | Yes                            |
| EU RoHS Directive      | Compliant  EU RoHS Declaration |
| Toxic heavy metal free | Yes                            |
| Mercury free           | Yes                            |

|                            |   |
|----------------------------|---|
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>     |
| RoHS exemption information |  <a href="#">Yes</a>                       |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|