

TCSESB083F2CU0

network switch, Modicon Networking, basic managed, 6 ports for copper, 2 ports for fiber optic, multimode



Main

Range of product	ConneXium
Product or component type	Ethernet TCP/IP managed switch
Concept	Transparent Ready
Communication port protocol	Ethernet TCP/IP HTTP HTTPS SNMP RS232 LLDP SNTP MRP (Media Redundancy Protocol)
Port Ethernet	10/100BASE-TX - 6 port(s) copper cable 100BASE-FX - 2 port(s) fiber optic
Maximum number of switches in cascade	Unlimited
Cybersecurity	Role-based access control

Complementary

Integrated connection type	Shielded RJ45 copper cable Duplex SC fiber optic
Transmission support medium	Twisted shielded pairs cable CAT 5E for fiber optic Multimode optical fiber for copper cable
Maximum cable distance between devices	100 m copper cable
Optic fiber length	4 Km 62.5/125 µm 5 km 50/125 µm
Attenuation	0...11 DB (62.2/125 µm) 0...8 dB (50/125 µm)
Ethernet service	Configuration via web server Multicast filtering Data stream control IGMP Snooping SNMP-Traps and SYSLOG
Communication service	TFTP Quality of Service (QoS) Port monitoring Port mirroring
Diagnostics run time	Signal contact Self test
Maximum number of switches in a ring	50
Redundancy	HiPER ring RSTP
[Us] rated supply voltage	12...24 V
Supply voltage limits	9.6...32 V DC SELV
Power consumption in W	8 W
Electrical connection	Removable connector 6 ways power supply
Mounting support	35 mm symmetrical DIN rail
Marking	CE UL RCM
Function available	System information

Local signalling	1 dual colour LED (green/yellow) for P1 P2 power supplies 1 LED (red) for fault 1 dual colour LED (green/yellow) for ring manager 1 LED (green) for stand-by 1 dual colour LED (green/yellow) for channel diagnostic Device status
Alarm output	1 voltfree contact 1 A
Alarm function	Power supply fault Data link status Switch fault Redundancy ring fault Switch fault Incorrect configuration Temperature threshold
Ethernet cabling system	TF switches
Width	74 mm
Height	131 mm
Depth	111 mm
Net weight	0.41 kg






Environment

Ambient air temperature for operation	0...60 °C
Relative humidity	10...95 % non-condensing
IP degree of protection	IP20
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Standards	UL 508 EN/IEC 61131
Product certifications	CE[RETURN]UL[RETURN]RCM

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.300 cm
Package 1 Width	16.100 cm
Package 1 Length	23.300 cm
Package 1 Weight	596.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	4
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.742 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions

